

## A10143 Strengthened hanging band

Hinged hanging band for SGP pipe

Part number A10143 Strengthened hanging band

Units (mm)

Size code	Diameter size (A)	Nominal diameter (B)	Applicable pipe outer diameter	t	C	Tightening bolt Dia. x Length	D	F
0011	15A	1/2	21.7	2.3	25	M 6×20	26	6
0026	20A	3/4	27.2	2.3	25	M 6×20	26	6
0045	25A	1	34.0	2.3	25	M 6×20	26	6
0050	32A	1 1/4	42.7	2.3	25	M 8×25	26	6
0064	40A	1 1/2	48.6	2.3	25	M 8×25	26	6
0079	50A	2	60.5	2.3	25	M 8×25	26	6
0083	65A	2 1/2	76.3	2.6	25	M10×30	26	6
0098	80A	3	89.1	2.6	25	M10×30	26	6
0115	90A	3 1/2	101.6	2.6	25	M10×30	26	6
0120	100A	4	114.3	2.6	25	M10×30	26	6
0134	125A	5	139.8	4.5	32	M12×45	36	11
0149	150A	6	165.2	4.5	32	M12×45	36	11
0153	200A	8	216.3	6.0	50	M16×50	55	15
0168	250A	10	267.4	6.0	50	M16×50	55	15
0172	300A	12	318.5	6.0	50	M16×50	55	15



## A11211 Dip-plated strengthened hanging band

Assembled hanging band for SGP pipe

Part number A11211 Dip-plated strengthened hanging band

Units (mm)

Size code	Diameter size (A)	Nominal diameter (B)	Applicable pipe outer diameter	t	C	Tightening bolt Dia. x Length	D	F
0018	15A	1/2	21.7	2.3	25	M 6×25	26	6
0022	20A	3/4	27.2	2.3	25	M 6×25	26	6
0037	25A	1	34.0	2.3	25	M 6×25	26	6
0041	32A	1 1/4	42.7	2.3	25	M 8×25	26	6
0056	40A	1 1/2	48.6	2.3	25	M 8×25	26	6
0075	50A	2	60.5	2.3	25	M 8×25	26	6
0080	65A	2 1/2	76.3	2.6	25	M10×30	26	6
0094	80A	3	89.1	2.6	25	M10×30	26	6
0107	100A	4	114.3	2.6	25	M10×30	26	6



## A10144 Strengthened hanging band with lock

Hinged hanging band for SGP pipe

Part number A10144 Strengthened hanging band with lock

Units (mm)

Size code	Diameter size (A)	Nominal diameter (B)	Applicable pipe outer diameter	t	C	Tightening bolt Dia. x Length	D	H	Hanging bolt diameter
0019	15A	1/2	21.7	2.3	25	M 6×20	26	73	W 3/8
0023	20A	3/4	27.2	2.3	25	M 6×20	26	76	W 3/8
0038	25A	1	34.0	2.3	25	M 6×20	26	79	W 3/8
0042	32A	1 1/4	42.7	2.3	25	M 8×25	26	83	W 3/8
0057	40A	1 1/2	48.6	2.3	25	M 8×25	26	86	W 3/8
0061	50A	2	60.5	2.3	25	M 8×25	26	92	W 3/8
0076	65A	2 1/2	76.3	2.6	25	M10×30	26	99	W 3/8
0095	80A	3	89.1	2.6	25	M10×30	26	105	W 3/8
0108	90A	3 1/2	101.6	2.6	25	M10×30	26	111	W 3/8
0112	100A	4	114.3	2.6	25	M10×30	26	118	W 3/8
0127	125A	5	139.8	4.5	32	M12×45	36	144	W 1/2
0131	150A	6	165.2	4.5	32	M12×45	36	157	W 1/2
0146	200A	8	216.3	6.0	50	M16×50	55	212	W 5/8
0165	250A	10	267.4	6.0	50	M16×50	55	238	W 5/8
0170	300A	12	318.5	6.0	50	M16×50	55	263	W 5/8

