


マシンリーマ Machine Reamer



公差 (Tolerance)	D					
	0.01トビ Increment 0.01	+0.005 0	3	+0.007 +0.002	3.1~ 6	+0.009 +0.004
	18.1~30	+0.017 +0.008	30.1~50	+0.02 +0.009	51 ~80	+0.024 +0.011
					6.1~ 10	+0.012 +0.006
					10.1~18	+0.015 +0.007
					81 ~100	+0.028 +0.013

右刃ストレート 食付角度45° SKH51
Straight Flute Chamfer Angle45° HSS

直径 (ϕD)	食付長 (T)	刃長 ($\ell 1$)	首長 ($\ell 2$)	全長 (L)	MTNo.	刃数 (N)	センタ
Dia.	Chamfer Length	Length of Flutes	Neck Length	Overall Length	Shank MTNo.	Number of Flutes	Center
3	0.5	35	9.5	110	1	6	60° 凹
3.1	0.5	35	9.5	110	1	6	60° 凹
3.2	0.5	35	9.5	110	1	6	60° 凹
3.3	0.5	35	9.5	110	1	6	60° 凹
3.4	0.5	35	9.5	110	1	6	60° 凹
3.5	0.5	35	9.5	110	1	6	60° 凹
3.6	0.5	35	9.5	110	1	6	60° 凹
3.7	0.5	35	9.5	110	1	6	60° 凹
3.8	0.5	35	9.5	110	1	6	60° 凹
3.9	0.5	35	9.5	110	1	6	60° 凹
4	0.5	35	9.5	110	1	6	60° 凹
4.1	0.5	45	9.5	120	1	6	60° 凹
4.2	0.5	45	9.5	120	1	6	60° 凹
4.3	0.5	45	9.5	120	1	6	60° 凹
4.4	0.5	45	9.5	120	1	6	60° 凹
4.5	0.5	45	9.5	120	1	6	60° 凹
4.6	1	45	9.5	120	1	6	60° 凹
4.7	1	45	9.5	120	1	6	60° 凹
4.8	1	45	9.5	120	1	6	60° 凹
4.9	1	45	9.5	120	1	6	60° 凹
5	1	45	9.5	120	1	6	60° 凹
5.1	1	45	9.5	120	1	6	60° 凹
5.2	1	45	9.5	120	1	6	60° 凹
5.3	1	45	9.5	120	1	6	60° 凹
5.4	1	45	9.5	120	1	6	60° 凹
5.5	1	45	9.5	120	1	6	60° 凹
5.6	1	50	14.5	130	1	6	60° 凹
5.7	1	50	14.5	130	1	6	60° 凹
5.8	1	50	14.5	130	1	6	60° 凹
5.9	1	50	14.5	130	1	6	60° 凹
6	1	50	14.5	130	1	6	60° 凹
6.1	1	50	14.5	130	1	6	60° 凹
6.2	1	50	14.5	130	1	6	60° 凹
6.3	1	50	14.5	130	1	6	60° 凹
6.4	1	50	14.5	130	1	6	60° 凹
6.5	1	50	14.5	130	1	6	60° 凹
6.6	1	55	19.5	140	1	6	60° 凹
6.7	1	55	19.5	140	1	6	60° 凹
6.8	1	55	19.5	140	1	6	60° 凹
6.9	1	55	19.5	140	1	6	60° 凹
7	1	55	19.5	140	1	6	60° 凹
7.1	1	55	19.5	140	1	6	60° 凹
7.2	1	55	19.5	140	1	6	60° 凹

直径 (ϕD)	食付長 (T)	刃長 ($\ell 1$)	首長 ($\ell 2$)	全長 (L)	MTNo.	刃数 (N)	センタ
Dia.	Chamfer Length	Length of Flutes	Neck Length	Overall Length	Shank MTNo.	Number of Flutes	Center
7.3	1	55	19.5	140	1	6	60° 凹
7.4	1	55	19.5	140	1	6	60° 凹
7.5	1	55	19.5	140	1	6	60° 凹
7.6	1	60	24.5	150	1	6	60° 凹
7.7	1	60	24.5	150	1	6	60° 凹
7.8	1	60	24.5	150	1	6	60° 凹
7.9	1	60	24.5	150	1	6	60° 凹
8	1	60	24.5	150	1	6	60° 凹
8.1	1	60	24.5	150	1	6	60° 凹
8.2	1	60	24.5	150	1	6	60° 凹
8.3	1	60	24.5	150	1	6	60° 凹
8.4	1	60	24.5	150	1	6	60° 凹
8.5	1	60	24.5	150	1	6	60° 凹
8.6	1	70	24.5	160	1	6	60° 凹
8.7	1	70	24.5	160	1	6	60° 凹
8.8	1	70	24.5	160	1	6	60° 凹
8.9	1	70	24.5	160	1	6	60° 凹
9	1	70	24.5	160	1	6	60° 凹
9.1	1	70	24.5	160	1	6	60° 凹
9.2	1	70	24.5	160	1	6	60° 凹
9.3	1	70	24.5	160	1	6	60° 凹
9.4	1	70	24.5	160	1	6	60° 凹
9.5	1	70	24.5	160	1	6	60° 凹
9.6	1	70	24.5	160	1	6	60° 凹
9.7	1	70	24.5	160	1	6	60° 凹
9.8	1	70	24.5	160	1	6	60° 凹
9.9	1	70	24.5	160	1	6	60° 凹
10	1	70	24.5	160	1	6	60° 凹
10.1	1	70	24.5	160	1	6	60° 凹
10.2	1	70	24.5	160	1	6	60° 凹
10.3	1	70	24.5	160	1	6	60° 凹
10.4	1	70	24.5	160	1	6	60° 凹
10.5	1	70	24.5	160	1	6	60° 凹
10.6	1	75	29.5	170	1	6	60° 凹
10.7	1	75	29.5	170	1	6	60° 凹
10.8	1	75	29.5	170	1	6	60° 凹
10.9	1	75	29.5	170	1	6	60° 凹
11	1	75	29.5	170	1	6	60° 凹
11.1	1	75	29.5	170	1	6	60° 凹
11.2	1	75	29.5	170	1	6	60° 凹
11.3	1	75	29.5	170	1	6	60° 凹
11.4	1	75	29.5	170	1	6	60° 凹
11.5	1	75	29.5	170	1	6	60° 凹