




Dimensions: Basic



● FJ-0-3 to 5




Rod nut dimensions





● FJ-0-6, 8, 10, 36 to 45

(Dust cover is not included with FJ-36 to 45)




Rod nut dimensions





● FJ-0-12 to 30

(Dust cover is not included with FJ-30)



Rod nut dimensions



*1: For FJ-3 to 5, strictly observe the screw-in depth (P).

Model No.	Major cylinders	M		A	B	C	D	E	F	G	H	J	N	P ^{*1}	Allowable eccentricity	Max. working tension and compression KN	Weight kg
		Nominal port size	Pitch												U		
FJ-O- 3	SCPD3-6/SMG-6	3	0.5	23	—	8.3	12	2.5	5.5	2.5	11	5.5	1.8	4	0.5	0.019	0.012
4	SCPD3-10/SMG-10	4	0.7	26	—	10	12	3.5	7	2.5	11	5.5	2.4	3.7	0.5	0.053	0.012
5	SCPD3-16/SSD/SSD2-12-N/SMG-16	5	0.8	31.6	—	12	15.5	4	8	3.5	14	7	3.2	5.2	0.5	0.121	0.022
6	SSD/SSD2-16-N/SMG-20	6	1.0	45.4	—	15.8	21	4	10	9	17	10	3.6	12	0.75	1.08	0.057
8	CMA2/CMK2/CKV2-20/JSK2/JSM2-20	8	1.0	48.4	—	18.8	21	4	13	9	17	10	5	12	0.75	1.08	0.061
8-1.25	SMG-25/SSD/SSD2-20-N/SCM-20	8	1.25	48.4	—	18.8	21	4	13	9	17	10	5	12	0.75	1.08	0.061
10	CMA2-30/SMG-32/CMK2/SCG/CKV2-25/32/FCD-25-N/SSD/SSD2-25-N/SCM-25/32/JSK2-25/32/JSM2-30	10	1.25	56.2	—	22	24	7	17	10	19	12	6	12	0.75	2.45	0.092
12	CMA2/CMK2/CKV2-40/JSK2/JSM2-40	12	1.5	58	20.5	23	27	6	19	10	21	12	7	11.8	0.75	2.45	0.12
12-1.25	-	12	1.25	58	20.5	23	27	6	19	10	21	12	7	11.8	0.75	2.45	0.12
14	SCG-40/SCA2-40/FCD-32/40-NSSD/SSD2-32/40-N/SCM-40/JSC3-40	14	1.5	68.5	20	22	32	7	22	13	27	14	8	16.5	1.0	5.88	0.22
16	CAV2-50COV2-50	16	1.5	84.2	26	29	43	11	24	14	27	16	10	16.9	1.5	10.8	0.4
18	SCG-50/63/SCA2-50/63/FCD-50/63-N/SSD/SSD2-50/63-N/SCM-50/63/JSC3-50/63	18	1.5	84.2	26	29	43	11	27	14	27	18	11	16.9	1.5	10.8	0.41
22	SCG-80/SCA2-80/SSD/SSD2-80-N/SCM-80/JSC3-80	22	1.5	102.5	31	34	53	14	32	17	32	22	13	17.2	2.0	17.6	0.75
26	SCG-100/SCA2-100/SSD/SSD2-100-N/SCM-100/JSC3-100	26	1.5	121.6	39	42	69	15	41	20	41	26	16	20.8	3.0	27.5	1.5
30	SCS2-125/140/JSC4-125/140	30	1.5	145.2	47	50	90	16	46	21	46	30	18	26	3.0	60.8	3.1
36	SCS2-160/JSC4-160	36	1.5	163.5	—	57	108	16	55	22	55	55	21	25	4.0	87.3	4.6
40	SCS2-180/JSC4-180	40	1.5	170.5	—	64	108	16	60	22	55	60	24	25	4.0	87.3	4.7
45	SCS2-200	45	1.5	199.5	—	72	118	18	70	24	60	70	27	35	4.0	108	7.0