


パイプリーマ Pipe Reamer



公差 (Tolerance)

d: $\begin{matrix} -0.02 \\ -0.05 \end{matrix}$

《PR》 1/16T 右刃ストレート 食付角度45° SKH51
1/16Taper Straight Flute Chamfer Angle45° HSS

呼び 寸法 <small>Size</small>	小径 (φD1) <small>First Dia.</small>	食付長 (T) <small>Chamfer Length</small>	刃長 (ℓ) <small>Length of Flutes</small>	大径 (D2) <small>Dia at Large End</small>	全長 (L) <small>Overall Length</small>	柄径 (φd) <small>Shank Dia.</small>	刃数 (N) <small>Number of Flutes</small>	センタ <small>Center</small>
1/8	8.025	1	19	9.213	54	8	6	60°凹
1/4	10.312	1	27	12	62	10	6	60°凹
3/8	13.716	1.5	27	15.404	65	12	6	60°凹
1/2	16.891	1.5	35	19.079	80	16	8	60°凹
3/4	22.251	1.5	35	24.439	83	20	8	60°凹
1"	28.017	1.5	45	30.83	95	26	10	60°凹
1" 1/4	36.678	2	45	39.491	100	32	10	60°凹
1" 1/2	42.775	2	45	45.588	108	40	12	60°凹
2"	54.84	2.5	45	57.653	115	50	12	60°凹