


STANDARD NIPPERS

60-125,150



No.	SIZE mm	WEIGHT g/w	CUTTING PERFORMANCE		PACKAGE SIZE H×W×Dmm	Quantity	JAN CODE
			STEEL WIRE mm	COPPER WIRE mm			
60-125	125	85	Φ1.2	Φ2.0	170×73×15	6	006054
60-150	150	115	Φ1.6	Φ2.6	200×73×15	6	006061




No.60-150

STANDARD NIPPERS

60S-125,150



No.	SIZE mm	WEIGHT g/w	CUTTING PERFORMANCE		PACKAGE SIZE H×W×Dmm	Quantity	JAN CODE
			STEEL WIRE mm	COPPER WIRE mm			
60S-125	125	80	Φ1.2	Φ2.0	170×73×15	6	006252
60S-150	150	120	Φ1.6	Φ2.6	200×73×15	6	006269



No.60S-150

MINI NIPPERS

12S-120




Thin blade design that can easily cut through wire rods.



Thin blade design makes these nippers suitable for cutting in narrow places.

No.	SIZE mm	WEIGHT g/w	CUTTING PERFORMANCE		PACKAGE SIZE H×W×Dmm	Quantity	JAN CODE
			STEEL WIRE mm	COPPER WIRE mm			
12S-120	120	75	Φ0.8	Φ1.2	170×73×15	6	001257




MINITECH BOARD NIPPERS

MTN03-135



Thin and light to reduce burden on hands. Excellent for cutting in narrow places.

No.	SIZE mm	WEIGHT g/w	CUTTING PERFORMANCE		PACKAGE SIZE H×W×Dmm	Quantity	JAN CODE
			STEEL WIRE mm	COPPER WIRE mm			
MTN03-135	135	65	Φ0.8	Φ1.3	200×73×17	6	080160



ELASTOMER Electro-static discharge model


MINITECH BOARD NIPPERS

MTN03E-135



Comes with an electrostatic discharge resistant resin grip for working with electronics, too.

No.	SIZE mm	WEIGHT g/w	CUTTING PERFORMANCE		PACKAGE SIZE H×W×Dmm	Quantity	JAN CODE
			STEEL WIRE mm	COPPER WIRE mm			
MTN03E-135	135	65	Φ0.8	Φ1.3	200×73×17	6	080177



※The last six digits of JAN (Japanese Article Numbering) Code are displayed with the manufacturer code [4952520] omitted.