


ハイス

## SPSCR

切削条件表

P132

ストレートシャンクスパイラルチャッキングリーマ Straight Shank Spiral Chucking Reamer



公差 (Tolerance)	D			d			
	0.01トピ Increment 0.01	+0.005 0	2 ~ 3		+0.007 +0.002	3.1~ 6	+0.009 +0.004
	6.1~10	+0.012 +0.006	10.1~18		+0.015 +0.007	18.1~30	+0.017 +0.008

右刃左ネジレ12° 食付角度45° SKH56  
Helix Angle-Left12° Chamfer Angle45° HSS-Co.

直径 (ΦD)	食付長 (T)	刃長 (ℓ1)	首長 (ℓ2)	全長 (L)	シャンク径 (Φd)	刃数 (N)	センタ
Dia.	Chamfer Length	Length of Flutes	Neck Length	Overall Length	Shank Dia.	Number of Flutes	Center
2	0.5	20	-	80	1.8	4	60°凸
2.1	0.5	20	-	80	1.8	4	60°凸
2.2	0.5	25	15	90	2	4	60°凸
2.3	0.5	25	15	90	2	4	60°凸
2.4	0.5	25	15	90	2.2	4	60°凸
2.5	0.5	25	15	90	2.2	4	60°凸
2.6	0.5	25	15	90	2.2	4	60°凸
2.7	0.5	30	30	110	2.5	6	60°凸
2.8	0.5	30	30	110	2.5	6	60°凸
2.9	0.5	30	30	110	2.5	6	60°凸
3	0.5	30	30	110	2.5	6	60°凸
3.1	0.5	30	30	110	2.5	6	60°凸
3.2	0.5	30	30	110	2.8	6	60°凸
3.3	0.5	30	30	110	2.8	6	60°凸
3.4	0.5	30	30	110	2.8	6	60°凸
3.5	0.5	30	30	110	2.8	6	60°凸
3.6	0.5	30	30	110	2.8	6	60°凸
3.7	0.5	30	30	110	3.5	6	60°凹
3.8	0.5	30	30	110	3.5	6	60°凹
3.9	0.5	30	30	110	3.5	6	60°凹
4	0.5	30	30	110	3.5	6	60°凹
4.1	0.5	30	30	110	3.5	6	60°凹
4.2	0.5	30	40	120	3.5	6	60°凹
4.3	0.5	30	40	120	3.5	6	60°凹
4.4	0.5	30	40	120	3.5	6	60°凹
4.5	0.5	30	40	120	3.5	6	60°凹
4.6	0.5	30	40	120	3.5	6	60°凹
4.7	1	30	40	120	4	6	60°凹
4.8	1	30	40	120	4	6	60°凹
4.9	1	30	40	120	4	6	60°凹
5	1	30	40	120	4	6	60°凹
5.1	1	30	40	120	4	6	60°凹
5.2	1	30	40	120	4.5	6	60°凹
5.3	1	30	40	120	4.5	6	60°凹
5.4	1	30	40	120	4.5	6	60°凹
5.5	1	30	40	120	4.5	6	60°凹
5.6	1	30	40	120	4.5	6	60°凹
5.7	1	30	40	130	5	6	60°凹
5.8	1	30	40	130	5	6	60°凹
5.9	1	30	40	130	5	6	60°凹
6	1	30	40	130	5	6	60°凹
6.1	1	30	40	130	5	6	60°凹
6.2	1	35	35	130	5	6	60°凹

直径 (ΦD)	食付長 (T)	刃長 (ℓ1)	首長 (ℓ2)	全長 (L)	シャンク径 (Φd)	刃数 (N)	センタ
Dia.	Chamfer Length	Length of Flutes	Neck Length	Overall Length	Shank Dia.	Number of Flutes	Center
6.3	1	35	35	130	5	6	60°凹
6.4	1	35	35	130	5	6	60°凹
6.5	1	35	35	130	5	6	60°凹
6.6	1	35	35	130	5	6	60°凹
6.7	1	35	45	140	6	6	60°凹
6.8	1	35	45	140	6	6	60°凹
6.9	1	35	45	140	6	6	60°凹
7	1	35	45	140	6	6	60°凹
7.1	1	35	45	140	6	6	60°凹
7.2	1	35	45	140	6	6	60°凹
7.3	1	35	45	140	6	6	60°凹
7.4	1	35	45	140	6	6	60°凹
7.5	1	35	45	140	6	6	60°凹
7.6	1	35	45	140	6	6	60°凹
7.7	1	40	40	150	6	6	60°凹
7.8	1	40	40	150	6	6	60°凹
7.9	1	40	40	150	6	6	60°凹
8	1	40	40	150	6	6	60°凹
8.1	1	40	40	150	6	6	60°凹
8.2	1	40	40	150	7	6	60°凹
8.3	1	40	40	150	7	6	60°凹
8.4	1	40	40	150	7	6	60°凹
8.5	1	40	40	150	7	6	60°凹
8.6	1	40	40	150	7	6	60°凹
8.7	1	40	50	160	7	6	60°凹
8.8	1	40	50	160	7	6	60°凹
8.9	1	40	50	160	7	6	60°凹
9	1	40	50	160	7	6	60°凹
9.1	1	40	50	160	7	6	60°凹
9.2	1	40	50	160	7	6	60°凹
9.3	1	40	50	160	7	6	60°凹
9.4	1	40	50	160	7	6	60°凹
9.5	1	40	50	160	7	6	60°凹
9.6	1	40	50	160	7	6	60°凹
9.7	1	40	50	160	8	6	60°凹
9.8	1	40	50	160	8	6	60°凹
9.9	1	40	50	160	8	6	60°凹
10	1	40	50	160	8	6	60°凹
10.1	1	40	50	160	8	6	60°凹
10.2	1	40	50	160	8	6	60°凹
10.3	1	40	50	160	8	6	60°凹
10.4	1	40	50	160	8	6	60°凹
10.5	1	40	50	160	8	6	60°凹

※60°凸は2013.6月規格変更あり