

Poli Light



Application

- Removal oxide film and rust ●Cleaning before welding or coating
- Cover the scratch mark and buff the surface of aluminum or copper. ●Adjustment surface roughness before painting and laminating.
- Seal cleaning ●Setting for mirror finish ●Light deburring metal part ●removing damage mark of FRP

Poli Light Disc S Poli Light Wheel

Poli Light Wheel

Poli Light Wheel T



From dia.30 to dia.100mm are available.

From dia. 10mm to dia. 30mm are available.

Poli Light Disc S

| item no. | dia × width × hole (mm) | RPM | grit | | | | | | | | | | | | | Q'ty/box | | | |
|-----------|-------------------------|--------|------|----|----|----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----------|------|---|---|
| | | | 36 | 46 | 60 | 80 | 100 | 120 | 150 | 180 | 240 | 320 | 400 | 600 | 800 | | 1000 | 0 | |
| PLD10016S | 100×10×16 | 13,000 | | | ● | ● | | | ● | ● | | | ● | ● | ● | | ● | | 5 |

Poli Light Wheel

| item no. | dia × width × shaft dia × shaft length(mm) | RPM | grit | | | | | | | | | | | | | Q'ty/box | | | |
|----------|--|--------|------|----|----|----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----------|------|---|---|
| | | | 36 | 46 | 60 | 80 | 100 | 120 | 150 | 180 | 240 | 320 | 400 | 600 | 800 | | 1000 | 0 | |
| PLW3025 | 30×25×6×40 | 12,000 | | | ● | ● | | | ● | ● | | | ● | ● | ● | | ● | | 5 |
| PLW4025 | 40×25×6×40 | 12,000 | | | ● | ● | | | ● | ● | | | ● | ● | ● | | ● | | 5 |
| PLW5025 | 50×25×6×40 | 10,000 | | | ● | ● | | | ● | ● | | | ● | ● | ● | | ● | | 5 |
| PLW6025 | 60×25×6×40 | 10,000 | | | ● | ● | | | ● | ● | | | ● | ● | ● | | ● | | 5 |
| PLW8025 | 80×25×6×40 | 8,000 | | | ● | ● | | | ● | ● | | | ● | ● | ● | | ● | | 5 |

Poli Light Wheel T

| item no. | dia × layer × shaft dia × shaft length(mm) | RPM | grit | | | | | | | | | | | | | Q'ty/box | | | |
|-------------|--|--------|------|----|----|----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----------|------|---|----|
| | | | 36 | 46 | 60 | 80 | 100 | 120 | 150 | 180 | 240 | 320 | 400 | 600 | 800 | | 1000 | 0 | |
| PLWT103P4P3 | 10×3P/4P×3×35 | 12,000 | | | ● | ● | | | ● | ● | | | ● | ● | ● | | ● | | 10 |
| PLWT153P4P3 | 15×3P/4P×3×35 | 12,000 | | | ● | ● | | | ● | ● | | | ● | ● | ● | | ● | | 10 |
| PLWT203P4P3 | 20×3P/4P×3×35 | 12,000 | | | ● | ● | | | ● | ● | | | ● | ● | ● | | ● | | 10 |
| PLWT253P4P3 | 25×3P/4P×3×35 | 12,000 | | | ● | ● | | | ● | ● | | | ● | ● | ● | | ● | | 10 |
| PLWT303P4P3 | 30×3P/4P×3×35 | 12,000 | | | ● | ● | | | ● | ● | | | ● | ● | ● | | ● | | 10 |

☆ For using Poli Light , please keep it dry operation. It ensure operation with oil-based buffing compound or abrasives. Avoid in wet operation with water of emulsifying oil due to weakness for water.