


UNI-JOINT PLUGS / HYDRO-CIRCUIT BLOCKS

— HEAT PROOF TYPE —

Uni-joint plugs



Part Number		L	L1	U/Price 1~9
Type	No.			
JWRH	1	50	65	Quotation
		65	100	

Use in atmospheric pressure 980kPa (10kgf/cm²) or lower.

Characteristics

The length can be adjusted within the L ~ L1 range.


Heat resistance is 180°C, and it can be used for both cooling water and oil.

Notes on handling


Install it in a balanced manner. The structure have allowance of about 1mm in height difference between right and left. However, if it is off balance, excessive load is applied onto the body, which may lead to water leakage.



Example



Hydro-circuit blocks




O-ring Size	W	W1	Part Number		U/Price 1~9
			Type	L	
JIS G40	95	75	BRJH	50	Quotation
JIS G60	125	105		80	
JIS G75	145	125		100	

Use in atmospheric pressure 980kPa (10kgf/cm²) or lower.



Example



φP6.0~7.0 is recommended hole diameter.
Heat resistance is 180°C, and it can be used for both cooling water and oil.



Order

Part Number — L

JWRH1 — 65
BRJH50



Days to Ship

Quotation



Price

Quotation