

NDXN-ASUS

INDEXING PLUNGERS




Stainless Steel


Heat resistance: 180°C



Type	Body	Knob	Spring	Nose
NDXN-ASUS	stainless steel (SUS303)	stainless steel (SUS303) Electropolished	stainless steel (SUS302WPA)	stainless steel (SUS420) Heat treated to Rc53-55
NDXN-W-ASUS				
NDXN-A-ASUS				stainless steel (SUS303)
NDXN-AW-ASUS				



NDXN-ASUS NDXN-A-ASUS
(Single-Nut)



NDXN-W-ASUS NDXN-AW-ASUS
(Double-Nut)

Type / Size	M	d (-0.02 -0.04)	L ₁	S	A	D	L	W ₁	T ₁	W	T	B	Force (N) Initial - Final	
NDXN-ASUS	6	M 6×0.75	3	12	3.5	0.8	14	34.5	8	5	10	3	2	4.5 – 9
	8	M 8×1	4	15	4	1	18	43	10	6	13	4		6 – 12
NDXN-W-ASUS	10	M10×1	5	17	5	1.3	21	50	13	7	17	5	3	5 – 12
NDXN-A-ASUS	12	M12×1.5	6	20	6	1.8	25	59	14	8	19	6		6 – 14
NDXN-AW-ASUS	16	M16×1.5	8	26	8	2.3	33	77	19	10	24	8	3	15 – 35
	20	M20×1.5	10	28	10	2.6		83	22	12	30	10		15 – 34