


**CON.REDUCERS**

R(C) OR CR



Size		OD1		OD2		Center to end	Unit:mm
Size A	Size B	I	II	I	II	H	
20Ax10A	3/4x3/8	26.9	25	17.3	14	38.0	
20Ax15A	3/4x1/2	26.9	25	21.3	18	38.0	
15Ax8A	1/2x1/4	21.3	18	13.7	10	-	
15Ax10A	1/2x3/8	21.3	18	17.3	14	-	
25Ax15A	1x1/2	33.7	32	21.3	18	51.0	
25Ax20A	1x3/4	33.7	32	26.7	25	51.0	
32Ax15A	1.1/4x1/2	42.4	38	21.3	18	51.0	
32Ax20A	1.1/4x3/4	42.4	38	26.9	25	51.0	
32Ax25A	1.1/4x1	42.4	38	33.7	32	51.0	
40Ax15A	1.1/2x1/2	48.3	45	21.3	18	64.0	
40Ax20A	1.1/2x3/4	48.3	45	26.9	25	64.0	
40Ax25A	1.1/2x1	48.3	45	33.7	32	64.0	
40Ax32A	1.1/2x1.1/4	48.3	45	42.4	38	64.0	
50Ax20A	2x3/4	60.3	57	26.9	25	76.0	
50Ax25A	2x1	60.3	57	33.7	32	76.0	
50Ax32A	2x1.1/4	60.3	57	42.4	38	76.0	
50Ax40A	2x1.1/2	60.3	57	48.3	45	76.0	
65Ax25A	2.1/2x1	73.0	76	33.7	32	89.0	
65Ax32A	2.1/2x1.1/4	73.0	76	42.4	38	89.0	
65Ax40A	2.1/2x1.1/2	73.0	76	48.3	45	89.0	
65Ax50A	2.1/2x2	73.0	76	60.3	57	89.0	
80Ax32A	3x1.1/4	88.9	89	42.4	38	89.0	
80Ax40A	3x1.1/2	88.9	89	48.3	45	89.0	
80Ax50A	3x2	88.9	89	60.3	57	89.0	
80Ax65A	3x2.1/2	88.9	89	73.0	76	89.0	
90Ax40A	3.1/2x1.1/2	101.6	-	48.3	-	102.0	
90Ax50A	3.2/2x2	101.6	-	60.3	-	102.0	
90Ax65A	3.1/2x2.1/2	101.6	-	73.0	-	102.0	
90Ax80A	3.1/2x3	101.6	-	88.9	-	102.0	
100Ax40A	4x1.1/2	114.3	108	48.3	45	102.0	
100Ax50A	4x2	114.3	108	60.3	57	102.0	
100Ax65A	4x2.1/2	114.3	108	73.0	76	102.0	
100Ax80A	4x3	114.3	108	88.9	89	102.0	
100Ax90A	4x3.1/2	114.3	-	101.6	-	102.0	
125Ax50A	5x2	141.3	133	60.3	57	127.0	
125Ax65A	5x2.1/2	141.3	133	73.0	76	127.0	
125Ax80A	5x3	141.3	133	88.9	89	127.0	
125Ax90A	5x3.1/2	141.3	-	101.6	-	127.0	
125Ax100A	5x4	141.3	133	114.3	133	127.0	
150Ax65A	6x2.1/2	168.3	159.0	73.0	76.0	140.0	
150Ax80A	6x3	168.3	159.0	88.9	89.0	140.0	
150Ax90A	6x3.1/2	168.3	-	101.6	-	140.0	
150Ax100A	6x4	168.3	159.0	114.3	108.0	140.0	
150Ax125A	6x5	168.3	159.0	141.3	133.0	140.0	

Size		OD1	OD2	Center to end	Unit:mm
Size A	Size B	m/m	m/m	H	
20Ax15A	3/4x1/2	27.2	21.7	38.1	
25Ax15A	1x1/2	34.0	21.7	50.8	
25Ax20A	1x3/4	34.0	27.2	50.8	
32Ax15A	1.1/4x1/2	42.7	21.7	50.8	
32Ax20A	1.1/4x3/4	42.7	27.2	50.8	
32Ax25A	1.1/4x1	42.7	34.0	50.8	
40Ax15A	1.1/2x1/2	48.6	21.7	63.5	
40Ax20A	1.1/2x3/4	48.6	27.2	63.5	
40Ax25A	1.1/2x1	48.6	34.0	63.5	
40Ax32A	1.1/2x1.1/4	48.6	42.7	63.5	
50Ax20A	2x3/4	60.5	27.2	76.2	
50Ax25A	2x1	60.5	34.0	76.2	
50Ax32A	2x1.1/4	60.5	42.7	76.2	
50Ax40A	2x1.1/2	60.5	48.6	76.2	
65Ax25A	2.1/2x1	76.3	34.0	88.9	
65Ax32A	2.1/2x1.1/4	76.3	42.7	88.9	
65Ax40A	2.1/2x1.1/2	76.3	48.6	88.9	
65Ax50A	2.1/2x2	76.3	60.5	88.9	
80Ax32A	3x1.1/4	89.1	42.7	88.9	
80Ax40A	3x1.1/2	89.1	48.6	88.9	
80Ax50A	3x2	89.1	60.5	88.9	
80Ax65A	3x2.1/2	89.1	76.3	88.9	
90Ax32A	3.1/2x1.1/4	101.6	42.7	101.6	
90Ax40A	3.1/2x1.1/2	101.6	48.6	101.6	
90Ax50A	3.1/2x2	101.6	60.5	101.6	
90Ax65A	3.1/2x2.1/2	101.6	76.3	101.6	
90Ax80A	3.1/2x3	101.6	89.1	101.6	
100Ax40A	4x1.1/2	114.3	48.6	101.6	
100Ax50A	4x2	114.3	60.5	101.6	
100Ax65A	4x2.1/2	114.3	76.3	101.6	
100Ax80A	4x3	114.3	89.1	101.6	
100Ax90A	4x3.1/2	114.3	101.6	101.6	
125Ax50A	5x2	139.8	60.5	127.0	
125Ax65A	5x2.1/2	139.8	76.3	127.0	
125Ax80A	5x3	139.8	89.1	127.0	
125Ax90A	5x3.1/2	139.8	101.6	127.0	
125Ax100A	5x4	139.8	114.3	127.0	
150Ax65A	6x2.1/2	165.2	76.3	139.7	
150Ax80A	6x3	165.2	89.1	139.7	
150Ax90A	6x3.1/2	165.2	101.6	139.7	
150Ax100A	6x4	165.2	114.3	139.7	
150Ax125A	6x5	165.2	139.8	139.7	

Size		Outside Diam		Center to end	Unit:mm
Size A	Size B	OD1	OD2	H	
20Ax10A	3/4x3/8	26.7	17.3	38.0	
20Ax15A	3/4x1/2	26.7	21.3	38.0	
15Ax8A	1/2x1/4	21.3	13.7	-	
15Ax10A	1/2x3/8	21.3	17.3	-	
25Ax15A	1x1/2	33.4	21.3	51.0	
25Ax20A	1x3/4	33.4	26.7	51.0	
32Ax15A	1.1/4x1/2	42.2	21.3	51.0	
32Ax20A	1.1/4x3/4	42.2	26.7	51.0	
32Ax25A	1.1/4x1	42.2	33.4	51.0	
40Ax15A	1.1/2x1/2	48.3	21.3	64.0	
40Ax20A	1.1/2x3/4	48.3	26.7	64.0	
40Ax25A	1.1/2x1	48.3	33.4	64.0	
40Ax32A	1.1/2x1.1/4	48.3	42.2	64.0	
50Ax20A	2x3/4	60.3	26.7	76.0	
50Ax25A	2x1	60.3	33.4	76.0	
50Ax32A	2x1.1/4	60.3	42.2	76.0	
50Ax40A	2x1.1/2	60.3	48.3	76.0	
65Ax25A	2.1/2x1	73.0	33.4	89.0	
65Ax32A	2.1/2x1.1/4	73.0	42.2	89.0	
65Ax40A	2.1/2x1.1/2	73.0	48.3	89.0	
65Ax50A	2.1/2x2	73.0	60.3	89.0	
80Ax32A	3x1.1/4	88.9	42.2	89.0	
80Ax40A	3x1.1/2	88.9	48.3	89.0	
80Ax50A	3x2	88.9	60.3	89.0	
80Ax65A	3x2.1/2	88.9	73.0	89.0	
90Ax40A	3.1/2x1.1/2	101.6	48.3	102.0	
90Ax50A	3.2/2x2	101.6	60.3	102.0	
90Ax65A	3.1/2x2.1/2	101.6	73.0	102.0	
90Ax80A	3.1/2x3	101.6	88.9	102.0	
100Ax40A	4x1.1/2	114.3	48.3	102.0	
100Ax50A	4x2	114.3	60.3	102.0	
100Ax65A	4x2.1/2	114.3	73.0	102.0	
100Ax80A	4x3	114.3	88.9	102.0	
100Ax90A	4x3.1/2	114.3	101.6	102.0	
125Ax50A	5x2	141.3	60.3	127.0	
125Ax65A	5x2.1/2	141.3	73.0	127.0	
125Ax80A	5x3	141.3	88.9	127.0	
125Ax90A	5x3.1/2	141.3	101.6	127.0	
125Ax100A	5x4	141.3	114.3	127.0	
150Ax65A	6x2.1/2	168.3	73.0	140.0	
150Ax80A	6x3	168.3	88.9	140.0	
150Ax90A	6x3.1/2	168.3	101.6	140.0	
150Ax100A	6x4	168.3	114.3	140.0	
150Ax125A	6x5	168.3	141.3	140.0	