



ねじれ半月ドリル 超硬
Spiral Gun Barrel Drill Carbide



ねじれ半月ドリル 超硬 DLCコーティング
Spiral Gun Barrel Drill Carbide DLC coating



超硬 シヤープ 1枚刃 右刃 140°

超硬 DLC シヤープ 1枚刃 右刃 140°

VAN Code No.	単位/寸法:mm 価格:円 Unit/Size:mm Price:JPY		在庫	参考価格
	直径φD	有効溝長 FL		
SHD0.1CB	0.1	0.6	●	¥6,000
SHD0.11CB	0.11	0.6	●	¥6,000
SHD0.12CB	0.12	0.7	●	¥6,000
SHD0.13CB	0.13	0.7	●	¥6,000
SHD0.14CB	0.14	0.7	●	¥6,000
SHD0.15CB	0.15	0.9	●	¥5,500
SHD0.16CB	0.16	0.9	●	¥5,500
SHD0.17CB	0.17	1	●	¥5,500
SHD0.18CB	0.18	1	●	¥5,500
SHD0.19CB	0.19	1	●	¥5,500
SHD0.2CB	0.2	1.2	●	¥5,000
SHD0.21CB	0.21	1.2	●	¥5,000
SHD0.22CB	0.22	1.2	●	¥5,000
SHD0.23CB	0.23	1.2	●	¥5,000
SHD0.24CB	0.24	1.2	●	¥5,000
SHD0.25CB	0.25	1.5	●	¥5,000
SHD0.26CB	0.26	1.5	●	¥5,000
SHD0.27CB	0.27	1.5	●	¥5,000
SHD0.28CB	0.28	1.5	●	¥5,000
SHD0.29CB	0.29	1.5	●	¥5,000
SHD0.3CB	0.3	1.8	●	¥4,000
SHD0.31CB	0.31	1.8	□	
SHD0.32CB	0.32	1.8	□	
SHD0.33CB	0.33	1.8	□	
SHD0.34CB	0.34	1.8	□	
SHD0.35CB	0.35	2.1	●	¥4,000
SHD0.36CB	0.36	2.1	□	
SHD0.37CB	0.37	2.1	□	
SHD0.38CB	0.38	2.1	□	
SHD0.39CB	0.39	2.1	□	
SHD0.4CB	0.4	2.4	●	¥4,000
SHD0.41CB	0.41	2.4	□	
SHD0.42CB	0.42	2.4	□	

VAN Code No.	単位/寸法:mm 価格:円 Unit/Size:mm Price:JPY		在庫	参考価格
	直径φD	有効溝長 FL		
SHD0.43CB	0.43	2.4	□	
SHD0.44CB	0.44	2.4	□	
SHD0.45CB	0.45	2.7	●	¥4,000
SHD0.46CB	0.46	2.7	□	
SHD0.47CB	0.47	2.7	□	
SHD0.48CB	0.48	2.7	□	
SHD0.49CB	0.49	2.7	□	
SHD0.5CB	0.5	3	●	¥4,000
SHD0.6CB	0.6	3.6	●	¥4,000
SHD0.7CB	0.7	4.2	●	¥4,000
SHD0.8CB	0.8	4.8	●	¥4,000
SHD0.9CB	0.9	5.4	●	¥4,000
SHD1.0CB	1	6	●	¥4,000
SHD1.1CB	1.1	6.6	●	¥4,000
SHD1.2CB	1.2	7.2	●	¥4,000
SHD1.3CB	1.3	7.8	●	¥4,000
SHD1.4CB	1.4	8.4	●	¥4,000
SHD1.5CB	1.5	9	●	¥4,000
SHD1.6CB	1.6	9.6	●	¥4,000
SHD1.7CB	1.7	10.2	●	¥4,000
SHD1.8CB	1.8	10.8	●	¥4,000
SHD1.9CB	1.9	11.4	●	¥4,000
SHD2.0CB	2	12	●	¥4,000
SHD2.1CB	2.1	12	●	¥4,000
SHD2.2CB	2.2	13.2	●	¥4,000
SHD2.3CB	2.3	13.2	●	¥4,000
SHD2.4CB	2.4	14.4	●	¥4,000
SHD2.5CB	2.5	14.4	●	¥4,000
SHD2.6CB	2.6	15.6	●	¥4,000
SHD2.7CB	2.7	15.6	●	¥4,000
SHD2.8CB	2.8	16.8	●	¥4,000
SHD2.9CB	2.9	16.8	●	¥4,000
SHD3.0CB	3	16.8	●	¥4,000

VAN Code No.	単位/寸法:mm 価格:円 Unit/Size:mm Price:JPY		在庫	参考価格
	直径φD	有効溝長 FL		
SHD0.1CBDLC	0.1	0.6	●	¥10,667
SHD0.11CBDLC	0.11	0.6	●	¥10,667
SHD0.12CBDLC	0.12	0.7	●	¥10,500
SHD0.13CBDLC	0.13	0.7	●	¥10,500
SHD0.14CBDLC	0.14	0.7	●	¥10,500
SHD0.15CBDLC	0.15	0.9	●	¥9,667
SHD0.16CBDLC	0.16	0.9	●	¥9,667
SHD0.17CBDLC	0.17	1	●	¥9,667
SHD0.18CBDLC	0.18	1	●	¥9,667
SHD0.19CBDLC	0.19	1	●	¥9,667
SHD0.2CBDLC	0.2	1.2	●	¥8,667
SHD0.21CBDLC	0.21	1.2	●	¥8,667
SHD0.22CBDLC	0.22	1.2	●	¥8,667
SHD0.23CBDLC	0.23	1.2	●	¥8,667
SHD0.24CBDLC	0.24	1.2	●	¥8,667
SHD0.25CBDLC	0.25	1.5	●	¥8,500
SHD0.26CBDLC	0.26	1.5	●	¥8,500
SHD0.27CBDLC	0.27	1.5	●	¥8,500
SHD0.28CBDLC	0.28	1.5	●	¥8,500
SHD0.29CBDLC	0.29	1.5	●	¥8,500
SHD0.3CBDLC	0.3	1.8	●	¥7,333
SHD0.31CBDLC	0.31	1.8	□	
SHD0.32CBDLC	0.32	1.8	□	
SHD0.33CBDLC	0.33	1.8	□	
SHD0.34CBDLC	0.34	1.8	□	
SHD0.35CBDLC	0.35	2.1	●	¥7,333
SHD0.36CBDLC	0.36	2.1	□	
SHD0.37CBDLC	0.37	2.1	□	
SHD0.38CBDLC	0.38	2.1	□	
SHD0.39CBDLC	0.39	2.1	□	
SHD0.4CBDLC	0.4	2.4	●	¥7,333
SHD0.41CBDLC	0.41	2.4	□	
SHD0.42CBDLC	0.42	2.4	□	

VAN Code No.	単位/寸法:mm 価格:円 Unit/Size:mm Price:JPY		在庫	参考価格
	直径φD	有効溝長 FL		
SHD0.43CBDLC	0.43	2.4	□	
SHD0.44CBDLC	0.44	2.4	□	
SHD0.45CBDLC	0.45	2.7	●	¥7,333
SHD0.46CBDLC	0.46	2.7	□	
SHD0.47CBDLC	0.47	2.7	□	
SHD0.48CBDLC	0.48	2.7	□	
SHD0.49CBDLC	0.49	2.7	□	
SHD0.5CBDLC	0.5	3	●	¥7,000
SHD0.6CBDLC	0.6	3.6	●	¥7,000
SHD0.7CBDLC	0.7	4.2	●	¥7,000
SHD0.8CBDLC	0.8	4.8	●	¥7,000
SHD0.9CBDLC	0.9	5.4	●	¥7,000
SHD1.0CBDLC	1	6	●	¥7,000
SHD1.1CBDLC	1.1	6.6	●	¥7,000
SHD1.2CBDLC	1.2	7.2	●	¥7,000
SHD1.3CBDLC	1.3	7.8	●	¥7,000
SHD1.4CBDLC	1.4	8.4	●	¥7,000
SHD1.5CBDLC	1.5	9	●	¥7,000
SHD1.6CBDLC	1.6	9.6	●	¥7,000
SHD1.7CBDLC	1.7	10.2	●	¥7,000
SHD1.8CBDLC	1.8	10.8	●	¥7,000
SHD1.9CBDLC	1.9	11.4	●	¥7,000
SHD2.0CBDLC	2	12	●	¥7,000
SHD2.1CBDLC	2.1	12	●	¥7,000
SHD2.2CBDLC	2.2	13.2	●	¥7,000
SHD2.3CBDLC	2.3	13.2	●	¥7,000
SHD2.4CBDLC	2.4	14.4	●	¥7,000
SHD2.5CBDLC	2.5	14.4	●	¥7,000
SHD2.6CBDLC	2.6	15.6	●	¥7,000
SHD2.7CBDLC	2.7	15.6	●	¥7,000
SHD2.8CBDLC	2.8	16.8	●	¥7,000
SHD2.9CBDLC	2.9	16.8	●	¥7,000
SHD3.0CBDLC	3	16.8	●	¥7,000

Stock ●・・・標準在庫品 / Stocked
Stock □・・・特定商社在庫品 / Stocked by Specific Distributors

■被削材適合性

Suitability for Work Materials

◎・・・最適 The most suitable ○・・・適 Suitable △・・・可 Possible 無印・・・不可 Impossible

製品区分 Product	軟鋼 Mild Steel	炭素鋼 Carbon Steel	合金鋼 Alloy Steel	調質鋼 Hardened Steel	工具鋼 Tool Steel	焼入れ鋼 Quenched & Tempered Steel	ステンレス鋼 Stainless Steel	鑄鉄 Cast Iron	タタリ鋼 Ductile Cast Iron	チタン合金 Titanium Alloy	アルミ合金 Aluminium Alloy	銅 Copper	プラスチック Plastic	セラミック etc. Ceramics etc.		
	SS	S45C	SCM SCR	SKD SKS	~40 HRC	~45 HRC	45~ HRC	SUS	FC	FDC		AI	Cu		マシナブル Machinable	ジルコニア ガラス Zirconia Glass
SHD-CB	◎	○	△		△						○	○	◎	◎		
SHD-CBDLC											○	◎	◎	◎		

- SP CENTER
- CENTER DRILL
- GP DRILL
- TFD
- SPIRAL GUN BARREL DRILL
- TOGLON SHARP SP
- TOGLON HARD
- CORNER ROUNDING CUTTER
- JIT
- SUBMARINE GATE DRILL
- MICRO TOOL
- TECHNICAL INFORMATION
- CUSTOMIZED TOOL SEMIORDER TOOL
- INST-RUCTION
- COMPANY PROFILE