



TYPE		BUTTERFLY				BUTTERFLY				BUTTERFLY				BUTTERFLY				BUTTERFLY			
Butterfly Valve																					
FIG		UV				FV				PN10EJMQ				PN10EJMW				PN10EJMF			
PRESSURE		Class 175				Class 175				PN10				PN10				PN10			
END CONNECTION		BS21 (JIS B0203)				BS21 (JIS B0203)				EN 1092 PN16				EN 1092 PN16				EN 1092 PN16			
DIMENSIONS		inch	mm	L	H	D	L	H	D	L	H	D	L	H	D	L	H	D			
	1/2	15	43	44	85	47	44	85	—	—	—	—	—	—	—	—	—	—			
	3/4	20	47	47	85	51	47	85	—	—	—	—	—	—	—	—	—	—			
	1	25	56	50	85	58	50	85	—	—	—	—	—	—	—	—	—	—			
	1 1/4	32	63	60	110	67	60	110	—	—	—	—	—	—	—	—	—	—			
	1 1/2	40	69	63	110	73	63	110	—	—	—	—	—	—	—	—	—	—			
	2	50	77	70	110	82	70	110	43	191	180	43	191	180	43	191	180	180			
	2 1/2	65	—	—	—	—	—	—	46	199	180	46	199	180	46	199	180	180			
	3	80	—	—	—	—	—	—	46	217	180	46	217	180	46	217	180	180			
	4	100	—	—	—	—	—	—	52	227	180	52	227	180	52	227	180	180			
	5	125	—	—	—	—	—	—	56	265	230	56	265	230	56	265	230	230			
	6	150	—	—	—	—	—	—	56	277	230	56	277	230	56	277	230	230			
	8	200	—	—	—	—	—	—	60	295	350	60	295	350	60	295	350	350			
10	250	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—				
12	300	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—	—				
BODY		Stainless Steel				Forged Brass				Ductile Iron				Ductile Iron				Ductile Iron			
STEM		Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel				Stainless Steel			
DISC		Stainless Steel+W-NBR				Stainless Steel+W-NBR				Stainless Steel				Stainless Steel				Stainless Steel			
SEAT		NBR				NBR				VMQ				W-NBR				FKM			

Bronze & Brass

Cast Iron

Ductile Iron

Stainless Steel

Carbon Steel

Butterfly Valve

Ball Valve

Ball Valve Seat

Actuated Valve