


KSE-2

超硬ソリッド 2 枚刃エンドミル
Tungsten Carbide 2 Flutes Solid Endmill

■刃径をΦ3~Φ6まで0.01とびにラインナップ
Line-upped Φ3~Φ6 at pitch 0.01



超微粒子合金 Micro Grain Tungsten Carbide



刃径の許容差 Flute Diameter Tolerance
D 0~-0.01



柄径の許容差 Shank Diameter Tolerance
d 0~-0.008



ネジレ角30° Twist Angle 30°



ピンカド Sharp Edge

●切削条件表はP124に記載
●Cutting conditions are recommended on page 124.

[寸法単位: mm]
[size: mm]

品番 Code No.	刃径 D Flute Diameter	刃長 ℓ Flute Length	全長 L Total Length	柄径 d Shank Diameter	備考 Remarks
KSE-2300	3	10	50	6	
KSE-2301	3.01	10	50	6	
KSE-2302	3.02	10	50	6	
KSE-2303	3.03	10	50	6	
KSE-2304	3.04	10	50	6	
KSE-2305	3.05	10	50	6	
KSE-2306	3.06	10	50	6	
KSE-2307	3.07	10	50	6	
KSE-2308	3.08	10	50	6	
KSE-2309	3.09	10	50	6	
KSE-2310	3.1	10	50	6	
KSE-2311	3.11	10	50	6	
KSE-2312	3.12	10	50	6	
KSE-2313	3.13	10	50	6	
KSE-2314	3.14	10	50	6	
KSE-2315	3.15	10	50	6	
KSE-2316	3.16	10	50	6	
KSE-2317	3.17	10	50	6	
KSE-2318	3.18	10	50	6	
KSE-2319	3.19	10	50	6	
KSE-2320	3.2	10	50	6	
KSE-2321	3.21	10	50	6	

品番 Code No.	刃径 D Flute Diameter	刃長 ℓ Flute Length	全長 L Total Length	柄径 d Shank Diameter	備考 Remarks
KSE-2322	3.22	10	50	6	
KSE-2323	3.23	10	50	6	
KSE-2324	3.24	10	50	6	
KSE-2325	3.25	10	50	6	
KSE-2326	3.26	10	50	6	
KSE-2327	3.27	10	50	6	
KSE-2328	3.28	10	50	6	
KSE-2329	3.29	10	50	6	
KSE-2330	3.3	10	50	6	
KSE-2331	3.31	10	50	6	
KSE-2332	3.32	10	50	6	
KSE-2333	3.33	10	50	6	
KSE-2334	3.34	10	50	6	
KSE-2335	3.35	10	50	6	
KSE-2336	3.36	10	50	6	
KSE-2337	3.37	10	50	6	
KSE-2338	3.38	10	50	6	
KSE-2339	3.39	10	50	6	
KSE-2340	3.4	10	50	6	
KSE-2341	3.41	10	50	6	
KSE-2342	3.42	10	50	6	
KSE-2343	3.43	10	50	6	
KSE-2344	3.44	10	50	6	
KSE-2345	3.45	10	50	6	
KSE-2346	3.46	10	50	6	
KSE-2347	3.47	10	50	6	
KSE-2348	3.48	10	50	6	
KSE-2349	3.49	10	50	6	
KSE-2350	3.5	10	50	6	
KSE-2351	3.51	10	50	6	
KSE-2352	3.52	10	50	6	
KSE-2353	3.53	10	50	6	
KSE-2354	3.54	10	50	6	
KSE-2355	3.55	10	50	6	
KSE-2356	3.56	10	50	6	
KSE-2357	3.57	10	50	6	
KSE-2358	3.58	10	50	6	
KSE-2359	3.59	10	50	6	
KSE-2360	3.6	10	50	6	
KSE-2361	3.61	10	50	6	
KSE-2362	3.62	10	50	6	
KSE-2363	3.63	10	50	6	
KSE-2364	3.64	10	50	6	
KSE-2365	3.65	10	50	6	
KSE-2366	3.66	10	50	6	
KSE-2367	3.67	10	50	6	
KSE-2368	3.68	10	50	6	
KSE-2369	3.69	10	50	6	