



MF Flange conforming to ISO1609 is used for error absorption and workability improvement by connecting with claw clamp. Also, by using single claw clamp, you can connect piping flange directly to vacuum chamber, and that could lead to reduction of BOM and space saving. Design and production of special shape in accordance with use environment are also available other than the catalog products.



ISO Bolt Flange

Material:SUS304



Code	Flange size	Connecting pipe	ϕA	ϕB	PCD	T	t	N	ϕh
MCM-1025	NW25	20A ($\phi 27.2$)	70	26.2	55	8	3	4	6.6
MCM-1032	NW32	25A ($\phi 34.0$)	90.0	34.2	70	8	3	4	9
MCM-1040	NW40	32A ($\phi 42.7$)	100	41.2	80	12	7	4	9
MCM-1050	NW50	40A ($\phi 48.6$)	110	52.2	90	12	7	4	9
MCM-1063	NW63	50A ($\phi 60.5$)	130	70.2	110	12	5	4	9
MCM-1080	NW80	65A ($\phi 76.3$)	145	83.0	125	12	5	8	9
MCM-1100	NW100	90A ($\phi 101.6$)	165	102.0	145	12	5	8	9
MCM-1125	NW125	100A ($\phi 114.3$)	200	127.2	175	16	9	8	11
MCM-1160	NW160	125A ($\phi 139.8$)	225	153.2	200	16	9	8	11
MCM-1200	NW200	200A ($\phi 216.3$)	285	214.0	260	16	9	12	11