

SIDE CUTTING PLIERS

2080 2080N

Slim type side cutting pliers


Stripping hole



2080-185



2080N-210



Model	Size (mm)	Dimensions(mm)			Weight (g)	Cutting capacity (φmm)	
		A	B	C		Steel wire	Copper wire
2080-185	185	20.0	12.0	33.0	214	3.2	4.0
2080-210	210	23.0	12.5	37.0	274	3.6	4.5
2080N-185	185	20.0	12.0	33.0	213	3.2	4.0
2080N-210	210	23.0	12.5	37.0	272	3.6	4.5


6050

Side cutting pliers
◀with crimping die▶

Crimping



Stripping hole




Model	Size (mm)	Dimensions(mm)			Weight (g)	Cutting capacity (φmm)	
		A	B	C		Steel wire	Copper wire
6050	185	24.0	14.0	33.0	295	2.6	3.5

XP200

Side cutting pliers
for electrical work



Elastomer cover



Model	Size (mm)	Dimensions(mm)			Weight (g)	Cutting capacity (φmm)	
		A	B	C		Steel wire	Copper wire
XP200	200	27.5	13.5	33.0	360	3.6	4.5

8050


Center cutting pliers



8050-185




8050-210



Model	Size (mm)	Dimensions(mm)			Weight (g)	Cutting capacity (φmm)		
		A	B	C		Steel wire	Copper wire	VVF
8050-185	185	23.0	11.7	30.5	235	3.2	4.0	1.6×2
8050-210	210	24.5	13.5	35.5	300	3.6	4.5	2.0×3

2070

High leverage
side cutting pliers



Model	Size (mm)	Dimensions(mm)			Weight (g)	Cutting capacity (φmm)	
		A	B	C		Steel wire	Copper wire
2070	225	27.0	12.4	38.5	360	4.0	5.0