

HEAT NIPPERS FOR CUTTING PLASTICS

Section of blade

Round type

Flat type


Angle type

HT170

<Angle blade type>

Spring Loaded

Flat type



| Model | Size (mm) | Weight (g) | Cutting capacity (φmm) | Blade length (mm) | Transformer | Heater |
|--------------|-----------|------------|------------------------|-------------------|-------------|--------|
| | | | Plastics | | | |
| HT170 | 150 | 275 | 4.0 | 22 | TRF25 | W19 |

HT180

<Standard type>

Spring Loaded

Round type



| Model | Size (mm) | Weight (g) | Cutting capacity (φmm) | Blade length (mm) | Transformer | Heater |
|--------------|-----------|------------|------------------------|-------------------|-------------|--------|
| | | | Plastics | | | |
| HT180 | 190 | 295 | 4.0 | 16 | TRF25 | W19 |

HT200

<Heavy-duty type>

Spring Loaded

Round type



| Model | Size (mm) | Weight (g) | Cutting capacity (φmm) | Blade length (mm) | Transformer | Heater |
|--------------|-----------|------------|------------------------|-------------------|-------------|--------|
| | | | Plastics | | | |
| HT200 | 190 | 375 | 7.0 | 23 | TRF25 | W29 |

TRF25

<100V . 220V . 240V >

TRF100D



TRF25

TRF25-120V will be sold in 2017 years



TRF100D

| Model | Input power | Output power | Length of cord (m) |
|----------------|---------------|--------------|--------------------|
| TRF25 | AC100V50·60HZ | 30VA MAX | 1.85 |
| TRF100D | AC100V50·60HZ | 30VA MAX | 1.83 |

HDT100

<Step-Down Transformer for TRF25-100V >

HEATER



HEATER

W-19 <24V-19W>

W-29 <24V-29W>



| Model | Input power | Output power | Length of cord (m) | Weight (g) |
|---------------|--------------|--------------|--------------------|------------|
| HDT100 | AC 220V~240V | AC 100V | 1.85 | 950 |