

NIPPERS

Blade shape **Standard**  for cutting hard wire


Semi-flush  for cutting medium wire

Full-flush  for cutting soft wire only or plastic, gate and sprue

205 ^{JIS}

Diagonal cutting nippers

Standard 




Model	Size (mm)	Dimensions(mm)			Weight (g)	Cutting capacity (φmm)	
		A	B	C		Steel wire	Copper wire
④ 205-150	150	22.0	12.5	22.5	185	2.0	2.6
④ 205-175	175	24.5	13.0	26.5	260	2.0	3.0
205-200	200	26.5	14.0	30.0	330	2.6	3.5

205H ^{JIS}

Diagonal cutting nippers

Standard 




Model	Size (mm)	Dimensions(mm)			Weight (g)	Cutting capacity (φmm)	
		A	B	C		Steel wire	Copper wire
④ 205H-150	150	22.0	12.5	22.5	195	2.0	2.6
④ 205H-175	175	24.5	13.0	26.5	270	2.0	3.0
205H-200	200	26.5	14.0	30.0	345	2.6	3.5

206S

Flush diagonal nippers

Spring Loaded

Full-flush 




Model	Size (mm)	Dimensions(mm)			Weight (g)	Cutting capacity (φmm)	
		A	B	C		Steel wire	Copper wire
206S-150	150	22.5	12.5	22.0	185	2.0	2.6
206S-175	175	24.5	13.0	26.5	260	2.0	3.0
206S-200	200	26.0	14.0	29.0	330	2.6	3.5

207

Diagonal cutting nippers
<with crimping die>

Standard 



Model	Size (mm)	Dimensions(mm)			Weight (g)	Cutting capacity (φmm)	
		A	B	C		Steel wire	Copper wire
207	225	26.0	12.2	27.0	347	3.0	4.0