

Diametral Tolerance of Bore

* Not greater than h11 is recommended

Basic dimension (mm)		h																	
		1	2	3	4	5	6	7	8	9	10	11	12	13	14	15	16	17	18
Over	Max.	Dimensional tolerance																	
		μm												mm					
-	3	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-0.8	-1.2	-2	-3	-4	-6	-10	-14	-25	-40	-60	-0.1	-0.14	-0.25	-0.4	-0.6		
3	6	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-1	-1.5	-2.5	-4	-5	-8	-12	-18	-30	-48	-75	-0.12	-0.18	-0.3	-0.48	-0.75	-1.2	-1.8
6	10	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-1	-1.5	-2.5	-4	-6	-9	-15	-22	-36	-58	-90	-0.15	-0.22	-0.36	-0.58	-0.9	-1.5	-2.2
10	18	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-1.2	-2	-3	-5	-8	-11	-18	-27	-43	-70	-110	-0.18	-0.27	-0.43	-0.7	-1.1	-1.8	-2.7
18	30	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-1.5	-2.5	-4	-6	-9	-13	-21	-33	-52	-84	-130	-0.21	-0.33	-0.52	-0.84	-1.3	-2.1	-3.3
30	50	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-1.5	-2.5	-4	-7	-11	-16	-25	-39	-62	-100	-160	-0.25	-0.39	-0.62	-1	-1.6	-2.5	-3.9
50	80	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-2	-3	-5	-8	-13	-19	-30	-46	-74	-120	-190	-0.3	-0.46	-0.74	-1.2	-1.9	-3	-4.6
80	120	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-2.5	-4	-6	-10	-15	-22	-35	-54	-87	-140	-220	-0.35	-0.54	-0.87	-1.4	-2.2	-3.5	-5.4
120	180	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-3.5	-5	-8	-12	-18	-25	-40	-63	-100	-160	-250	-0.4	-0.63	-1	-1.6	-2.5	-4	-6.3
180	250	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-4.5	-7	-10	-14	-20	-29	-46	-72	-115	-185	-290	-0.46	-0.72	-1.15	-1.85	-2.9	-4.6	-7.2
250	315	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-6	-8	-12	-16	-23	-32	-52	-81	-130	-210	-320	-0.52	-0.81	-1.3	-2.1	-3.2	-5.2	-8.1
315	400	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-7	-9	-13	-18	-25	-36	-57	-89	-140	-230	-360	-0.57	-0.89	-1.4	-2.3	-3.6	-5.7	-8.9
400	500	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-8	-10	-15	-20	-27	-40	-63	-97	-155	-250	-400	-0.63	-0.97	-1.55	-2.5	-4	-6.3	-9.7
500	630	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-9	-11	-16	-22	-32	-44	-70	-110	-175	-280	-440	-0.7	-1.1	-1.75	-2.8	-4.4	-7	-11
630	800	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-10	-13	-18	-25	-36	-50	-80	-125	-200	-320	-500	-0.8	-1.25	-2	-3.2	-5	-8	-12.5
800	1000	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-11	-15	-21	-28	-40	-56	-90	-140	-230	-360	-560	-0.9	-1.4	-2.3	-3.6	-5.6	-9	-14
1000	1250	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-13	-18	-24	-33	-47	-66	-105	-165	-260	-420	-660	-1.05	-1.65	-2.6	-4.2	-6.6	-10.5	-16.5
1250	1600	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-15	-21	-29	-39	-55	-78	-125	-195	-310	-500	-780	-1.25	-1.95	-3.1	-5	-7.8	-12.5	-19.5
1600	2000	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-18	-25	-35	-46	-65	-92	-150	-230	-370	-600	-920	-1.5	-2.3	-3.7	-6	-9.2	-15	-23
2000	2500	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-22	-30	-41	-55	-78	-110	-175	-280	-440	-700	-1100	-1.75	-2.8	-4.4	-7	-11	-17.5	-28
2500	3150	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0	0
		-26	-36	-50	-68	-96	-135	-210	-330	-540	-860	-1350	-2.1	-3.3	-5.4	-8.6	-13.5	-21	-33