

# NIPPERS

Blade shape

Standard



for cutting hard wire

Semi-flush



for cutting medium wire

Full-flush





for cutting soft wire only or plastic, gate and sprue

## 450

Diagonal cutting nippers

Spring Loaded

Semi-flush




| Model   | Size (mm) | Dimensions (mm) |      |      | Weight (g) | Cutting capacity (φ mm) |             |
|---------|-----------|-----------------|------|------|------------|-------------------------|-------------|
|         |           | A               | B    | C    |            | Steel wire              | Copper wire |
| 450-125 | 125       | 12.5            | 8.0  | 14.0 | 70         | 0.8                     | 1.2         |
| 450-150 | 150       | 17.0            | 10.0 | 20.5 | 130        | 1.5                     | 2.6         |

## 305

Wire nippers  
<for hard wire>

Spring Loaded

Standard




| Model | Size (mm) | Dimensions (mm) |      |      | Weight (g) | Cutting capacity (φ mm) |             |
|-------|-----------|-----------------|------|------|------------|-------------------------|-------------|
|       |           | A               | B    | C    |            | Steel wire              | Copper wire |
| 305-7 | 175       | 24.0            | 12.5 | 20.0 | 195        | 2.6                     | 3.5         |
| 305-8 | 200       | 26.5            | 12.5 | 23.0 | 245        | 3.2                     | 4.0         |

## WA1000

Compound cutting nippers

Spring Loaded

Standard



| Model  | Size (mm) | Dimensions (mm) |      |      | Weight (g) | Cutting capacity (φ mm) |             |
|--------|-----------|-----------------|------|------|------------|-------------------------|-------------|
|        |           | A               | B    | C    |            | Steel wire              | Copper wire |
| WA1000 | 160       | 19.0            | 11.0 | 17.0 | 160        | 2.0                     | 2.6         |


## XN200

Diagonal cutting nippers  
for electrical work

Standard



Elastomer cover




| Model | Size (mm) | Dimensions (mm) |      |      | Weight (g) | Cutting capacity (φ mm) |             |
|-------|-----------|-----------------|------|------|------------|-------------------------|-------------|
|       |           | A               | B    | C    |            | Steel wire              | Copper wire |
| XN200 | 200       | 26.5            | 13.5 | 28.0 | 330        | 2.6                     | 3.5         |

## 205T

Diagonal cutting nippers  
<Luminous cover>

Standard



| Model    | Size (mm) | Dimensions (mm) |      |      | Weight (g) | Cutting capacity (φ mm) |             |
|----------|-----------|-----------------|------|------|------------|-------------------------|-------------|
|          |           | A               | B    | C    |            | Steel wire              | Copper wire |
| 205T-150 | 150       | 22.0            | 12.5 | 22.5 | 191        | 2.0                     | 2.6         |
| 205T-175 | 175       | 24.5            | 13.0 | 26.5 | 243        | 2.0                     | 3.0         |
| 205T-200 | 200       | 26.5            | 14.0 | 30.0 | 324        | 2.6                     | 3.5         |