


# FCTA-C / FCTS-C T-Cross Clamper



WEB Selection  
Tool

WEB CAD  
Download

SUS Stainless steel



\*Dimensional allowance before slit machining.

FCTS-C



FCTA-C

- The clamper joints 2 shafts with T-shaped cross.
- Clamping Type. Mounting shaft and removing shaft are easy. Moreover this does not scratch the shaft.
- Space-saving layout is possible.
- Convenient for fixing of side guide and sensors of the conveyance line.
- Light aluminum and stainless steel with highly corrosion-resistant are standardized.
- Compatible with both round shaft and square shaft.
- All products are provided with hex socket head cap screw.

## Material/Finish

RoHS Compliant

	FCTA-C Made of Aluminum	FCTS-C Made of Stainless Steel
Main body	A6063 Barrel Polishing	SUS304 Barrel Polishing
with Hexagon Socket Bolt	SUSXM7	SUSXM7 Molybdenum Disulfide Coating

Unit : mm

Part Number Aluminum	Mass (g)	Part Number Stainless steel	Mass (g)	D1	D2	B1*1	A	W	L	H	F1	F2	M (coarse)
FCTA-8-10-C	37	FCTS-8-10-C	111	8	10		22	35	12.5	11	5.5	3.7	M3
FCTA-10-10-C	36	FCTS-10-10-C	106	10	10	8	22	35	12.5	11	5.5	3.7	M3
FCTA-12-12-C	52	FCTS-12-12-C	154	12	12	10	25	40	14.5	12.5	6	3.8	M3
FCTA-15-15-C	93	FCTS-15-15-C	276	15	15	12	30	50	18	15.5	7	4.5	M4
FCTA-20-20-C	187	FCTS-20-20-C	553	20	20	16	38	63	21.5	20	9	5.5	M5

\*1 Dimensional allowance before slit machining.

- Part number specification

## FCTA-15-15-C



Cleanroom Wash & Packaging → P.792	Screw Length Adjustment → P.796	Vibration Resistant → P.795	Laser Marking → P.806
Available / Add'l charge	Not Available	Please feel free to contact us	Available / Add'l charge