



RoHS Compliant


ERON®

No.E-428Q

## Injection Clamps Type Q

Type	Material	Heat Treatment	Surface Treatment
Clamp bar	FCAD900	—	Cationic coating
Step Blocks	S45C	—	Blackened
Washer	S45C	HRC30±5 heat treatment	Blackened

- Mold base can be clamped quickly.
- The clamps and step blocks are connected, and cannot be lost.
- The slotted hole of the clamp is open, making it easy to insert and remove from the side.



### Specifications

Order No.	No.	Compatible Bolts	A	B	C	D	E	F	G	H	I	J	K	L	M	N	O	P	Weight (kg)
62518	ICQ12	M12	80	37	15	10	8	13	12	20	25	5	35	13	20	25	30	35	0.78
62519	ICQ16	M16	100	47	15	10	8	17	15	20	25	5	45	17	20	25	30	35	1.2
62520	ICQ20	M20	150	60	20	10	8	21	19.5	40	45	5	58	21	40	45	50	55	2.5
62521	ICQ24	M24	200	75	30	10	12	25	25	40	45	5	60	25	40	45	50	55	4.0

Base Elements

Clamp Units

Clamping Parts

Machine Vises

Drilling Vises

Vibration Isolation

Surface Plates and Measurement Instruments

Index