


# PJB Bushing for Locating Pin - Flange Type



WEB Selection Tool    WEB CAD Download



- Use it in combination with stepped locating pin **PJP** (→ P.494).

- Material/Finish

RoHS Compliant

	<b>PJB</b>
Main body	SK5 (hardness: 60 HRC or above)

Unit : mm

Part Number	d							D	R	H	T	Applicable positioning pin <b>PJP</b> → P.494	Mass (g)
	1	2	3	4	5	6	7						
<b>PJB-3</b>	3	6	8	10	12			7	0.8	11	2.5	PJP-3-**	3.3 - 4.8
<b>PJB-4</b>	4		8	10	12	16		8	1	12	3	PJP-4-**	4.8 - 7.2
<b>PJB-5</b>	5		8	10	12	16		10	1	14	3	PJP-5-**	7 - 11
<b>PJB-6</b>	6		8	10	12	16		10	1	14	3	PJP-6-**	6.2 - 9.5
<b>PJB-8</b>	8			10	12	16	20	12	2	16	4	PJP-8-**	9.9 - 15
<b>PJB-10</b>	10			10	12	16	20	15	2	19	4	PJP-10-**	14 - 22
<b>PJB-12</b>	12					16	20	18	2	22	4	PJP-12-**	27 - 37

- Part number specification

## PJB-6-16

Product Code **1** **2**

Cleanroom Wash & Packaging → P.792

Not Available

Vibration Resistant → P.795

Not Available

Laser Marking → P.806

Not Available