


- 鋼、型鋼、アルミまで、高速・高効率加工ができます。
- オーステナイト系ステンレス鋼には使用できません。

This drill having jobbers length is suitable for high-speed and long life drilling. This drill is not applied to Ausutenaite Stainless Steels.



LIST 7570P

オーダ方法

SGES 直径

切削条件 Drilling Condition ▶▶▶A-230

単位 (Unit): mm / 円 (¥)

直径 Dc	溝長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
2.0	24	56	3	●	1,240
2.1	24	56	3	●	1,240
2.2	25	56	3	●	1,240
2.3	25	56	3	●	1,240
2.4	30	61	3	●	1,240
2.5	30	61	3	●	1,240
2.6	30	61	3	●	1,240
2.7	33	64	3	●	1,240
2.8	33	64	3	●	1,240
2.9	33	64	3	●	1,240
3.0	33	64	3	●	1,240
3.1	36	68	4	●	1,470
3.2	36	68	4	●	1,470
3.3	36	68	4	●	1,470
3.4	39	71	4	●	1,470
3.5	39	71	4	●	1,470
3.6	39	71	4	●	1,620
3.7	39	71	4	●	1,620
3.8	43	75	4	●	1,620
3.9	43	75	4	●	1,620
4.0	43	75	4	●	1,620
4.1	43	85	6	●	1,820
4.2	43	85	6	●	1,820
4.3	47	89	6	●	1,820
4.4	47	89	6	●	1,820
4.5	47	89	6	●	1,820
4.6	47	89	6	●	2,060
4.7	47	89	6	●	2,060
4.8	52	94	6	●	2,060
4.9	52	94	6	●	2,060
5.0	52	94	6	●	2,060
5.1	52	94	6	●	2,460
5.2	52	94	6	●	2,460
5.3	52	94	6	●	2,460
5.4	57	99	6	●	2,460
5.5	57	99	6	●	2,460
5.6	57	99	6	●	2,640
5.7	57	99	6	●	2,640
5.8	57	99	6	●	2,640
5.9	57	99	6	●	2,640
6.0	57	99	6	●	2,640
6.1	63	107	8	●	2,870
6.2	63	107	8	●	2,870
6.3	63	107	8	●	2,870
6.4	63	107	8	●	2,870
6.5	63	107	8	●	2,870
6.6	63	107	8	●	3,000
6.7	63	107	8	●	3,000
6.8	69	113	8	●	3,000
6.9	69	113	8	●	3,000
7.0	69	113	8	●	3,000
7.1	69	113	8	●	3,190
7.2	69	113	8	●	3,190
7.3	69	113	8	●	3,190
7.4	69	113	8	●	3,190
7.5	69	113	8	●	3,190
7.6	75	119	8	●	3,280
7.7	75	119	8	●	3,280
7.8	75	119	8	●	3,280
7.9	75	119	8	●	3,280

直径 Dc	溝長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
8.0	75	119	8	●	3,280
8.1	75	125	10	●	3,620
8.2	75	125	10	●	3,620
8.3	75	125	10	●	3,620
8.4	75	125	10	●	3,620
8.5	75	125	10	●	3,620
8.6	81	131	10	●	3,850
8.7	81	131	10	●	3,850
8.8	81	131	10	●	3,850
8.9	81	131	10	●	3,850
9.0	81	131	10	●	3,850
9.1	81	131	10	●	4,090
9.2	81	131	10	●	4,090
9.3	81	131	10	●	4,090
9.4	81	131	10	●	4,090
9.5	81	131	10	●	4,090
9.6	87	137	10	●	4,500
9.7	87	137	10	●	4,500
9.8	87	137	10	●	4,500
9.9	87	137	10	●	4,500
10.0	87	137	10	●	4,500
10.1	87	144	12	●	4,850
10.2	87	144	12	●	4,850
10.3	87	144	12	●	4,850
10.4	87	144	12	●	4,850
10.5	87	144	12	●	4,850
10.6	87	144	12	●	5,370
10.7	94	151	12	●	5,370
10.8	94	151	12	●	5,370
10.9	94	151	12	●	5,370
11.0	94	151	12	●	5,370
11.1	94	151	12	●	6,030
11.2	94	151	12	●	6,030
11.3	94	151	12	●	6,030
11.4	94	151	12	●	6,030
11.5	94	151	12	●	6,030
11.6	94	151	12	●	6,540
11.7	94	151	12	●	6,540
11.8	94	151	12	●	6,540
11.9	101	158	12	●	6,540
12.0	101	158	12	●	6,540
12.1	101	158	12	●	7,300
12.2	101	158	12	●	7,300
12.3	101	158	12	●	7,300
12.4	101	158	12	●	7,300
12.5	101	158	12	●	7,300
12.6	101	158	12	●	7,660
12.7	101	158	12	●	7,660
12.8	101	158	12	●	7,660
12.9	101	158	12	●	7,660
13.0	101	158	12	●	7,660
13.1	101	158	12	□	-
13.2	101	158	12	□	-
13.3	108	168	16	□	-
13.4	108	168	16	□	-
13.5	108	168	16	●	11,900
13.6	108	168	16	□	-
13.7	108	168	16	□	-
13.8	108	168	16	□	-
13.9	108	168	16	□	-

