


# LSD

## ストレートシャンクロングドリル

Straight Shank Long Drills

●もっとも広い用途で 사용되는汎用のロングドリルです。

This is general HSS long drills for deep holes.



切削条件 Drilling Condition : A-238

単位 (Unit) : mm / 円 (¥)

LIST 550

オーダ方法

LSD 直径 × 全長 (□商品: LSD 直径 × 全長 × 溝長)

直径 Dc	全長 L	溝長 l	在庫 Stock	参考価格 Price
1.0	75	35	●	886
1.0	75	40	□	-
1.0	100	40	●	1,060
1.0	100	50	□	-
1.0	125	50	□	-
1.0	150	60	□	-
1.0	200	75	□	-
1.05	100	50	□	-
1.05	150	60	□	-
1.1	75	35	●	937
1.1	75	40	□	-
1.1	100	40	●	1,140
1.1	100	50	□	-
1.1	125	50	□	-
1.1	150	60	□	-
1.1	200	75	□	-
1.15	100	50	□	-
1.15	150	60	□	-
1.2	75	35	●	868
1.2	75	40	□	-
1.2	100	40	●	1,050
1.2	100	50	□	-
1.2	125	50	□	-
1.2	150	60	□	-
1.2	200	75	□	-
1.25	100	50	□	-
1.25	150	60	□	-
1.3	75	35	●	819
1.3	75	40	□	-
1.3	100	40	●	1,040
1.3	100	50	□	-
1.3	125	50	□	-
1.3	150	60	□	-
1.3	200	75	□	-
1.35	100	50	□	-
1.35	150	60	□	-
1.4	75	35	●	801
1.4	75	40	□	-
1.4	100	40	●	1,030
1.4	100	50	□	-
1.4	125	50	□	-
1.4	150	60	□	-
1.4	200	75	□	-
1.45	100	50	□	-
1.45	150	60	□	-
1.5	75	35	●	701
1.5	75	40	□	-
1.5	100	40	●	886
1.5	100	50	□	-
1.5	125	50	□	-
1.5	150	60	□	-
1.5	200	75	□	-
1.55	100	50	□	-
1.55	150	60	□	-
1.6	75	35	●	748
1.6	75	40	□	-
1.6	100	40	●	946
1.6	100	50	□	-
1.6	125	60	□	-
1.6	150	60	□	-
1.6	200	80	□	-
1.6	250	100	□	-
1.65	100	50	□	-
1.65	150	60	□	-
1.7	75	35	●	748
1.7	75	40	□	-

直径 Dc	全長 L	溝長 l	在庫 Stock	参考価格 Price
1.7	100	40	●	946
1.7	100	50	□	-
1.7	125	60	□	-
1.7	150	60	□	-
1.7	200	80	□	-
1.7	250	100	□	-
1.75	100	50	□	-
1.75	150	60	□	-
1.8	75	35	●	748
1.8	75	40	□	-
1.8	100	40	●	946
1.8	100	50	□	-
1.8	125	60	□	-
1.8	150	60	□	-
1.8	200	80	□	-
1.8	250	100	□	-
1.85	100	50	□	-
1.85	150	60	□	-
1.9	75	35	●	748
1.9	75	40	□	-
1.9	100	40	●	946
1.9	100	50	□	-
1.9	125	60	□	-
1.9	150	60	□	-
1.9	200	80	□	-
1.9	250	100	□	-
1.95	100	50	□	-
1.95	150	60	□	-
2.0	75	40	□	-
2.0	100	40	●	811
2.0	100	50	□	-
2.0	125	65	□	-
2.0	150	60	●	979
2.0	150	75	□	-
2.0	200	80	□	-
2.0	300	120	□	-
2.05	100	50	□	-
2.05	150	80	□	-
2.1	100	40	●	894
2.1	100	50	□	-
2.1	125	65	□	-
2.1	150	60	●	1,080
2.1	150	75	□	-
2.1	200	80	□	-
2.1	250	100	□	-
2.1	300	120	□	-
2.15	100	50	□	-
2.15	150	80	□	-
2.2	100	40	●	894
2.2	100	50	□	-
2.2	125	65	□	-
2.2	150	60	●	1,080
2.2	150	75	□	-
2.2	200	80	□	-
2.2	250	100	□	-
2.2	300	120	□	-
2.25	100	50	□	-
2.25	150	80	□	-
2.3	100	40	●	894
2.3	100	50	□	-
2.3	125	65	□	-
2.3	150	60	●	1,080
2.3	150	75	□	-
2.3	200	80	□	-
2.3	250	100	□	-

シャンク部の径はドリル直径よりもマイナスに仕上げられています。溝長の長いドリルでは大きなマイナスとなるために、ドリルコレットをご使用の場合には、締め代に余裕があるコレットを選定ください。詳細は H-20 を参照ください。