

SSB-B / SSBS-B Stopper Bolt - Head Sphere Type


Recommendation



WEB Selection Tool

WEB CAD Download


SUS Stainless steel



SSB-B

SSBS-B

- Usage example
Use the lock nut on an opposite side of the side that receives the force.



- Hexagon head is round.
- Round part has already been quenched. It is highly abrasion-resistant.
- All products are provided with lock nut.

Material/Finish

RoHS Compliant

	SSB-B Made of Steel	SSBS-B Made of Stainless Steel
Thread	S45C	SUS410
Part	Sphere part quenching (hardness: 45 HRC or above) Ferrosferic Oxide Film (Black)	Sphere part quenching (hardness: 40 HRC or above)
Nut	SS400 Trivalent Chromate Treatment	SUS304

Dimensions

Unit : mm

Part Number Steel	Part Number Stainless steel	M (coarse)	L2	T	R	L1	B	C	Mass (g)
SSB-M3-B		M3	1.5	2.4	6	2	5.5	6.4	1 - 2
SSB-M4-B		M4	2.1	3.2	8	2.8	7	8.1	2.3 - 5.2
SSB-M5-B		M5	2.4	4	8	3.5	8	9.2	3.7 - 9.7
SSB-M6-B	SSBS-M6-B	M6	3	5	10	4	10	11.5	7.2 - 15
SSB-M8-B	SSBS-M8-B	M8	3.7	6.5	12	5.5	13	15	15 - 40
SSB-M10-B		M10	4.5	8	16	7	17	19.6	38 - 63
SSB-M12-B		M12	5.2	10	20	8	19	21.9	54 - 99
SSB-M16-B		M16	6	13	25	10	24	27.7	108 - 155

SSB-B Made of Steel SSBS-B Made of Stainless Steel

Part Number	L (mm)											
	10	15	20	25	30	35	40	50	60	70	80	
SSB-M3-B	●	●	●	●	●							
SSB-M4-B	●	●	●	●	●	●	●					
SSB-M5-B	●	●	●	●	●	●	●	●				
SSB-M6-B		●	●	●	●	●	●	●				
SSB-M8-B		●	●	●	●	●	●	●	●			
SSB-M10-B					●	●	●	●	●	●		
SSB-M12-B					●	●	●	●	●	●	●	
SSB-M16-B						●	●	●	●	●	●	
SSBS-M6-B					●		●	●				
SSBS-M8-B					●		●	●				

Related Products

The stop pin with excellent abrasion resistance **SPM** is available for the stopper bolt recipient.

➔ P.538



- Part number specification

SSB-M10-30-B

Product Code Head Sphere Type

Cleanroom Wash & Packaging ➔ P.792

Screw Combination ➔ P.798

Screw Length Adjustment ➔ P.796

Vibration Resistant ➔ P.795

Please feel free to contact us

Not Available

Available / Add'l charge

Available / Add'l charge