


# SL4GE

G ロングエンドミル 4枚刃  
G End Mills Long Four Flutes

- 汎用コーティングエンドミルです。
  - 幅の広い側面や深い位置の側面加工に適しています。
- This is general coated long end mills for long side milling.



LIST 6212P  
オーダ方法

切削条件 Milling Condition ▶▶▶ B-273

SL4GE 外径

単位 (Unit): mm / 円 (¥)


外径 Dc	刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
3	15	60	6	●	3,240
4	20	60	8	●	3,240
5	25	65	8	●	3,240
6	25	65	8	●	3,240
7	35	80	10	●	3,720
8	35	80	10	●	3,720
9	45	95	10	●	4,160
10	45	95	10	●	4,160
11	55	105	12	●	5,150
12	55	105	12	●	5,150
13	55	110	16	●	6,640
14	55	110	16	●	6,640
15	65	120	16	●	7,340
16	65	120	16	●	8,190
17	65	130	20	●	9,980
18	65	130	20	●	9,980
19	75	140	20	●	11,600
20	75	140	20	●	11,600
21	75	140	20	●	14,600
22	75	140	20	●	14,600
23	90	160	25	●	17,900
24	90	160	25	●	17,900
25	90	160	25	●	17,900
26	90	160	25	●	19,900
27	90	160	25	●	23,700
28	90	160	25	●	23,700
29	90	160	25	●	28,400
30	90	160	25	●	28,400
31	105	190	32	●	34,900
32	105	190	32	●	34,900
33	105	190	32	●	43,300
34	105	190	32	●	43,300
35	105	190	32	●	43,300
36	105	190	32	●	45,900
37	125	210	32	●	51,200
38	125	210	32	●	51,200
39	125	210	32	●	60,200
40	125	210	32	●	60,200

外径 (mm) Dc		許容差 (mm) Tolerance
を超え Above	以下 Up to	
	10	+0.020~0
	30	+0.025~0
	30	+0.030~0

# SL4SE

スーパーハード ロング 4枚刃  
SUPER HARD End Mills Long Four Flutes

- 汎用エンドミルです。
  - 幅の広い側面や深い位置の側面加工に適しています。
- This is general long end mill for long side milling.



LIST 6212  
オーダ方法

切削条件 Milling Condition ▶▶▶ B-275

SL4SE 外径

単位 (Unit): mm / 円 (¥)

外径 Dc	刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	参考価格 Price
3	15	60	6	●	2,510
4	20	60	8	●	2,510
5	25	65	8	●	2,510
6	25	65	8	●	2,510
7	35	80	10	●	2,880
8	35	80	10	●	2,880
9	45	95	10	●	3,260
10	45	95	10	●	3,260
11	55	105	12	●	4,030
12	55	105	12	●	4,030
13	55	110	16	●	5,160
14	55	110	16	●	5,160
15	65	120	16	●	5,710
16	65	120	16	●	6,370
17	65	130	20	●	7,770
18	65	130	20	●	7,770
19	75	140	20	●	8,940
20	75	140	20	●	8,940
21	75	140	20	●	11,400
22	75	140	20	●	11,400
23	90	160	25	●	14,100
24	90	160	25	●	14,100
25	90	160	25	●	14,100
26	90	160	25	●	15,200
27	90	160	25	●	18,400
28	90	160	25	●	18,100
29	90	160	25	●	22,000
30	90	160	25	●	21,600
31	105	190	32	●	27,300
32	105	190	32	●	26,900
33	105	190	32	●	33,700
34	105	190	32	●	33,300
35	105	190	32	●	33,300
36	105	190	32	●	35,100
37	125	210	32	●	39,800
38	125	210	32	●	39,300
39	125	210	32	●	46,800
40	125	210	32	●	46,100

外径 (mm) Dc		許容差 (mm) Tolerance
を超え Above	以下 Up to	
	10	+0.020~0
	30	+0.025~0
	30	+0.030~0