




●生材から型鋼までの深穴加工に最適です。

Ideal for deep hole drilling from Unhardened Steel to Die Steel.



LIST 6538

オーダ方法 **商品記号**

単位 (Unit) : mm

| 商品記号 Code | 直径 DC | 溝長 LCF | 全長 OAL | 先端 PL | 在庫 Stock | 参考価格 (円) Price (¥) |
|--------------|----------|-----------|-----------|----------|-------------|-----------------------|
| AGPSLSD1.0 | 1.0 | 26 | 48 | 0.3 | | 1,550 |
| AGPSLSD1.1 | 1.1 | 28 | 50 | | | 1,810 |
| AGPSLSD1.2 | 1.2 | 30 | 52 | 0.4 | | 1,710 |
| AGPSLSD1.3 | 1.3 | | | | | 1,810 |
| AGPSLSD1.4 | 1.4 | 33 | 55 | | | 1,810 |
| AGPSLSD1.5 | 1.5 | | | | | 1,740 |
| AGPSLSD1.6 | 1.6 | 35 | 58 | 0.5 | | 1,860 |
| AGPSLSD1.7 | 1.7 | | | | | 2,040 |
| AGPSLSD1.8 | 1.8 | 38 | 62 | | | 1,940 |
| AGPSLSD1.9 | 1.9 | | | | | 1,940 |
| AGPSLSD2.0 | 2.0 | 41 | 66 | 0.6 | | 1,600 |
| AGPSLSD2.1 | 2.1 | | | | | 2,310 |
| AGPSLSD2.2 | 2.2 | 44 | 70 | | | 2,310 |
| AGPSLSD2.3 | 2.3 | | | | | 2,100 |
| AGPSLSD2.4 | 2.4 | 47 | 74 | | | 2,310 |
| AGPSLSD2.5 | 2.5 | | | | | 2,100 |
| AGPSLSD2.6 | 2.6 | 51 | 79 | 0.8 | | 2,100 |
| AGPSLSD2.7 | 2.7 | | | | | 2,100 |
| AGPSLSD2.8 | 2.8 | 51 | 79 | | | 2,230 |
| AGPSLSD2.9 | 2.9 | | | | | 2,100 |
| AGPSLSD3.0 | 3.0 | 55 | 84 | 0.9 | | 2,100 |
| AGPSLSD3.1 | 3.1 | | | | | 2,510 |
| AGPSLSD3.2 | 3.2 | 60 | 91 | | | 2,510 |
| AGPSLSD3.3 | 3.3 | | | | | 2,510 |
| AGPSLSD3.4 | 3.4 | 60 | 91 | 1.1 | | 2,790 |
| AGPSLSD3.5 | 3.5 | | | | | 2,790 |
| AGPSLSD3.6 | 3.6 | 64 | 96 | | | 2,790 |
| AGPSLSD3.7 | 3.7 | | | | | 2,790 |
| AGPSLSD3.8 | 3.8 | 64 | 96 | 1.2 | | 2,790 |
| AGPSLSD3.9 | 3.9 | | | | | 2,790 |
| AGPSLSD4.0 | 4.0 | 69 | 102 | | | 2,790 |
| AGPSLSD4.1 | 4.1 | | | | | 3,110 |
| AGPSLSD4.2 | 4.2 | 69 | 102 | 1.3 | | 3,110 |
| AGPSLSD4.3 | 4.3 | | | | | 3,110 |
| AGPSLSD4.4 | 4.4 | 74 | 108 | | | 3,110 |
| AGPSLSD4.5 | 4.5 | | | | | 3,110 |
| AGPSLSD4.6 | 4.6 | 74 | 108 | 1.4 | | 3,520 |
| AGPSLSD4.7 | 4.7 | | | | | 3,520 |
| AGPSLSD4.8 | 4.8 | 74 | 108 | | | 3,520 |
| AGPSLSD4.9 | 4.9 | | | | | 3,520 |
| AGPSLSD5.0 | 5.0 | 80 | 116 | 1.5 | | 3,520 |
| AGPSLSD5.1 | 5.1 | | | | | 4,560 |
| AGPSLSD5.2 | 5.2 | 80 | 116 | | | 4,560 |
| AGPSLSD5.3 | 5.3 | | | | | 4,560 |
| AGPSLSD5.4 | 5.4 | 80 | 116 | 1.6 | | 4,560 |
| AGPSLSD5.5 | 5.5 | | | | | 4,560 |
| AGPSLSD5.6 | 5.6 | 86 | 124 | 1.7 | | 4,600 |
| AGPSLSD5.7 | 5.7 | | | | | 4,600 |
| AGPSLSD5.8 | 5.8 | 86 | 124 | | | 4,600 |
| AGPSLSD5.9 | 5.9 | | | | | 4,600 |
| AGPSLSD6.0 | 6.0 | 86 | 124 | 1.8 | | 4,600 |
| AGPSLSD6.1 | 6.1 | | | | | 5,480 |
| AGPSLSD6.2 | 6.2 | 86 | 124 | | | 5,480 |
| AGPSLSD6.3 | 6.3 | | | | | 5,480 |
| AGPSLSD6.4 | 6.4 | 86 | 124 | 1.9 | | 5,480 |
| AGPSLSD6.5 | 6.5 | | | | | 5,480 |
| AGPSLSD6.6 | 6.6 | 93 | 133 | | | 5,670 |
| AGPSLSD6.7 | 6.7 | | | | | 5,670 |
| AGPSLSD6.8 | 6.8 | 93 | 133 | 2.0 | | 5,670 |
| AGPSLSD6.9 | 6.9 | | | | | 5,670 |
| AGPSLSD7.0 | 7.0 | 93 | 133 | 2.1 | | 5,670 |
| AGPSLSD7.1 | 7.1 | | | | | 5,670 |

| 商品記号 Code | 直径 DC | 溝長 LCF | 全長 OAL | 先端 PL | 在庫 Stock | 参考価格 (円) Price (¥) |
|--------------|----------|-----------|-----------|----------|-------------|-----------------------|
| AGPSLSD7.0 | 7.0 | 93 | 133 | 2.1 | | 5,670 |
| AGPSLSD7.1 | 7.1 | | | | | 6,040 |
| AGPSLSD7.2 | 7.2 | 93 | 133 | 2.2 | | 6,040 |
| AGPSLSD7.3 | 7.3 | | | | | 6,040 |
| AGPSLSD7.4 | 7.4 | 93 | 133 | | | 6,040 |
| AGPSLSD7.5 | 7.5 | | | | | 6,040 |
| AGPSLSD7.6 | 7.6 | 100 | 142 | 2.3 | | 6,430 |
| AGPSLSD7.7 | 7.7 | | | | | 6,430 |
| AGPSLSD7.8 | 7.8 | 100 | 142 | | | 6,430 |
| AGPSLSD7.9 | 7.9 | | | | | 6,430 |
| AGPSLSD8.0 | 8.0 | 100 | 142 | 2.4 | | 6,430 |
| AGPSLSD8.1 | 8.1 | | | | | 7,110 |
| AGPSLSD8.2 | 8.2 | 100 | 142 | | | 7,110 |
| AGPSLSD8.3 | 8.3 | | | | | 7,110 |
| AGPSLSD8.4 | 8.4 | 100 | 142 | 2.5 | | 7,110 |
| AGPSLSD8.5 | 8.5 | | | | | 7,110 |
| AGPSLSD8.6 | 8.6 | 107 | 151 | 2.6 | | 7,450 |
| AGPSLSD8.7 | 8.7 | | | | | 7,450 |
| AGPSLSD8.8 | 8.8 | 107 | 151 | | | 7,450 |
| AGPSLSD8.9 | 8.9 | | | | | 7,450 |
| AGPSLSD9.0 | 9.0 | 107 | 151 | 2.7 | | 7,450 |
| AGPSLSD9.1 | 9.1 | | | | | 8,630 |
| AGPSLSD9.2 | 9.2 | 107 | 151 | | | 8,630 |
| AGPSLSD9.3 | 9.3 | | | | | 8,630 |
| AGPSLSD9.4 | 9.4 | 116 | 162 | 2.8 | | 8,630 |
| AGPSLSD9.5 | 9.5 | | | | | 8,630 |
| AGPSLSD9.6 | 9.6 | 116 | 162 | 2.9 | | 9,620 |
| AGPSLSD9.7 | 9.7 | | | | | 9,620 |
| AGPSLSD9.8 | 9.8 | 116 | 162 | | | 9,620 |
| AGPSLSD9.9 | 9.9 | | | | | 10,700 |
| AGPSLSD10.0 | 10.0 | 125 | 173 | 3.0 | | 9,620 |
| AGPSLSD10.5 | 10.5 | | | | | 12,800 |
| AGPSLSD11.0 | 11.0 | 125 | 173 | 3.2 | | 13,600 |
| AGPSLSD11.5 | 11.5 | | | | | 15,000 |
| AGPSLSD12.0 | 12.0 | 134 | 184 | 3.3 | | 16,200 |
| AGPSLSD12.5 | 12.5 | | | | | 21,000 |
| AGPSLSD13.0 | 13.0 | 134 | 184 | 3.8 | | 22,400 |
| | | | | 3.9 | | 22,400 |

新商品

超硬ドリル

ハイスドリル

タップ

超硬
エンドミル

ハイス
エンドミル

切断工具

パック・
セット商品
その他

精密工具

技術資料
索引

| 一般 構造用鋼 | 炭素鋼 | 合金鋼 調質鋼 | ダイス鋼 プリハードン鋼 | 高硬度鋼 | |
|------------------|--------------|---------------|-----------------|-----------|----------|
| SS400 | S45C S50C | SCM NAK | 30~40 HRC | 40~50 HRC | 50~65HRC |
| — | ◎ | ◎ | ◎ | × | × |
| ステンレス鋼 | | Ti 合金 耐熱合金 | 鋳鉄 | アルミ合金 | 銅合金 |
| SUS304 SUS316 | SUS420 | Ti / Ni Alloy | FC / FCD | AC / ADC | Cu |
| × | — | — | ◎ | — | — |

◎: 最適 Excellent ○: 適用 Good ×: 不適 Not Used -: 推奨しません Not recommended