


SFB/SFBS Socket Button Head Cap Screws with Flange New Variation Added

[WEB Selection Tool](#)
[WEB CAD Download](#)
[SUS Stainless steel](#)
[Protrusion](#)



- Socket button head cap screws with wide bearing surface and are resistant to looseness.
- Intended for reducing the size of devices and applications with limited overhead space.
- Compared to **SFB** (Ferrosoferic Oxide Coating), **SFB-EL** (Electroless nickel plating) has excellent corrosion resistance.
- Application
Reducing the size of equipment and devices

● Material/Finish

RoHS Compliant

	SFB	SFBS	SFB-EL
Main Body	SCM435AD Ferrosoferic Oxide Coating (Black)	SUSXM7 (S.S. grade : A2)	SCM435AD Electroless nickel plating
Strength Class	10.9	A2-50	10.9

SFB Steel - Ferrosoferic Oxide Coating

Unit : mm

Part Number	M	L								D1	D2	L1	t1	B	t	Lb	Max. Torque (N·m)	Mass (g)
SFB-M3	M3	6	8	10	12					7	5.2	1.65	0.6	2	1.05	1	1	0.52 - 0.78
SFB-M4	M4	6	8	10	12	16	20			9.2	6.8	2.2	0.7	2.5	1.3	1.4	2	1 - 2
SFB-M5	M5		8	10	12	16	20	25		11.4	8.5	2.75	0.9	3	1.6	1.6	4	2 - 4
SFB-M6	M6		8	10	12	16	20	25		13.6	10.1	3.3	1	4	2.1	2	8	3 - 5.9
SFB-M8	M8			10	12	16	20	25		17	12.6	4.4	1.4	5	2.6	2.5	12	6.8 - 11

Part Number	Qty*1 per pack
SFB-M3	50
SFB-M4	50
SFB-M5	20
SFB-M6	20
SFB-M8	20

*1 1 The minimum order quantity is 1 piece. → P.794

[1 Individual Sales → P.794](#)
[Cleanroom Wash & Packaging → P.792](#)
[Screw Length Adjustment → P.796](#)
[Vibration Resistant → P.795](#)
[Modification process for captive use → P.791](#)
 Available / Add'l charge Available / Add'l charge Available / Add'l charge Available / Add'l charge Please feel free to contact us