


# SNS-EL Socket Head Cap Screws - Electroless Nickel Plating



WEB Selection Tool

WEB CAD Download

High strength



- Our unique processing technology enables screws to meet strength class 12.9 after surface treatment.
- For applications that require both high strength (Strength Class 12.9) and corrosion resistance.

### • Application

Equipment and device structures, FPD production equipment, semiconductor devices, and general industrial machines

### • Material/Finish

RoHS Compliant

	SNS-EL
Main Body	SCM435 Electroless Nickel Plating
Strength Class	12.9

Unit : mm

Part Number	M	L										D1	L1	B	Mass (g)	
SNS-M3-EL	M3	5	6	8	10	12	16	20				5.5	3	2.5	0.67 - 1.4	
SNS-M4-EL	M4	5	6	8	10	12	16	20	25			7	4	3	1.4 - 3.2	
SNS-M5-EL	M5		6	8	10	12	16	20	25			8.5	5	4	2.2 - 4.8	
SNS-M6-EL	M6			8	10	12	16	20	25	30		10	6	5	4.3 - 8.3	
SNS-M8-EL	M8				10	12	16	20	25	30	35	13	8	6	10 - 19	
SNS-M10-EL	M10							20	25	30	35	40	16	10	8	23 - 33

Part Number	Qty*1 per pack
SNS-M3-EL	20
SNS-M4-EL	20
SNS-M5-EL	20
SNS-M6-EL	10
SNS-M8-EL	10
SNS-M10-EL	10

\*1 The minimum order quantity is 1 piece. → P.794

### • Part number specification

## SNS - M5 - 16 - EL

Product Code **1** **2** Product Code

Order in number of packs.

The minimum order quantity is 1 piece. → P.794

Individual Sales → P.794	Cleanroom Wash & Packaging → P.792	Screw Length Adjustment → P.796	Vibration Resistant → P.795	Modification process for captive use → P.791
Available / Add'l charge	Available / Add'l charge	Not Available	Available / Add'l charge	Please feel free to contact us