


- 鋼、ステンレス鋼、アルミに適した汎用のコーティングオイルホールドリルです。
- 深い穴加工に最適です。

This is general coated taper shank long drills with oil-hole, and has rich variation of flute.



新商品

超硬ドリル

オーダー方法 GLTDOH 直径 × 全長  
直径5.0~10.0 在庫品限り

単位 (Unit) : mm

直径 DC	全長 LF	溝長 ℓ	先端 PL	シャンク MT No.	給油方式 Coolant Supply	在庫 Stock
5.0	300	200	1.5	2	2・3	□
5.0	350	230				
5.0	400	280				
5.0	450	300				
5.0	500	350				
5.5	300	200	1.7			
5.5	350	230				
5.5	400	280				
6.0	300	200	1.8			
6.0	350	230				
6.0	400	280				
6.0	450	300				
6.0	500	350	2.0			
6.5	300	200				
6.5	350	230				
6.5	400	280	2.1			
7.0	300	200				
7.0	350	230				
7.0	400	280				
7.0	450	300	2.3			
7.0	500	350				
7.5	300	200				
7.5	350	230	2.4			
7.5	400	280				
8.0	300	200				
8.0	350	230				
8.0	400	280	2.6			
8.0	450	300				
8.0	500	350				
8.0	600	400				
8.5	300	200	2.7			
8.5	350	230				
8.5	400	280				
9.0	300	200				
9.0	350	230	2.9			
9.0	400	280				
9.0	450	300				
9.0	500	350				
9.0	600	400	3.0			
9.5	300	200				
9.5	350	230				
9.5	400	280				
10.0	300	200	3.2			
10.0	350	230				
10.0	400	280				
10.0	500	350				
10.0	600	400	3.3			
10.0	800	600				
10.5	300	200				
10.5	350	230				
10.5	400	280	3.5			
11.0	300	200				
11.0	350	230				
11.0	400	280				
11.0	450	300	3.6			
11.0	500	350				
11.0	600	400				
11.0	800	600				
11.5	300	200				
11.5	350	230				
11.5	400	280				
12.0	300	200				
12.0	350	230				

直径 DC	全長 LF	溝長 ℓ	先端 PL	シャンク MT No.	給油方式 Coolant Supply	在庫 Stock
12.0	400	280	3.6	2	2・3	□
12.0	450	300				
12.0	500	350				
12.0	600	400				
12.0	800	600				
12.5	300	200	3.8			
12.5	350	230				
12.5	400	280				
12.5	450	300				
12.5	500	350	3.9			
12.5	600	400				
13.0	300	200				
13.0	350	230				
13.0	400	280	4.1			
13.0	450	300				
13.0	500	350				
13.0	600	400				
13.0	800	600	4.2			
13.5	300	200				
13.5	350	230				
13.5	400	280				
13.5	450	300	4.4			
13.5	500	350				
13.5	600	400				
14.0	300	200				
14.0	350	230	4.5			
14.0	400	280				
14.0	450	300				
14.0	500	350				
14.0	600	400	4.7			
14.0	800	600				
14.5	350	230				
14.5	400	260				
14.5	500	350	4.8			
14.5	600	400				
15.0	350	220				
15.0	400	260				
15.0	500	350	5.0			
15.0	600	400				
15.0	800	600				
15.5	350	220				
15.5	400	260	5.1			
15.5	500	350				
15.5	600	400				
16.0	350	220				
16.0	400	260	5.3			
16.0	450	300				
16.0	500	350				
16.0	600	400				
16.0	800	600				
16.5	350	220				
16.5	400	260				
16.5	500	350				
16.5	600	400				
17.0	350	220				
17.0	400	260				
17.0	450	300				
17.0	500	350				
17.0	600	400				
17.0	800	600				
17.5	350	220				
17.5	400	260				
17.5	500	350				
17.5	600	400				