


● LONG PLIERS SERIES



LONG PLIERS SERIES


STRAIGHT LONG NOSE CUTTING PLIERS, LONG

No.	L	ℓ	D	▼g	⊞
PS6-302	295	72	73	300	5

CONNECTOR HOUSING PLIERS

ANGLED LONG NOSE CUTTING PLIERS, LONG TYPE

No.	L	Angle	D	▼g	⊞
PS6-304	290	45°	73	300	5



● SIDE CUTTING PLIERS (COATED HANDLE)



SIDE CUTTING PLIERS (COATED HANDLE) JIS

No.	Nominal	Max. Cutting Dia.	L	▼g	⊞
SPD-150C	150	wireø2.15	165	215	10
-175C	175	wireø2.75	190	275	10
-200C	200	wireø3.4	215	375	10

- For cutting copper & steel wire and gripping & bending wires, thin plates, small parts, etc.
- Suitable for steel wire & sheet metal working.
- With vinyl coated handle. (No insulation)



● SIDE CUTTING PLIERS



SIDE CUTTING PLIERS JIS

No.	Nominal	Max. Cutting Dia.	L	▼g	⊞
SPD-175	175	wireø2.75	185	265	10

- For cutting copper & steel wire and gripping & bending wires, thin plates, small parts, etc.
- Suitable for steel wire & sheet metal working.




● NEEDLE NOSE PLIERS (STANDARD TYPE) PAT.P.



NEEDLE NOSE PLIERS (STANDARD TYPE)

No.	Max Cutting Dia.		L	ℓ	W ₁	W ₂	T ₁	T ₂	▼g	⊞
	soft	hard								
PSL-150	ø2.0	ø1.6	165	54	54	16	14	9	110	5
-200	ø2.3	ø1.8	205	70	55	18	15.5	10	190	5




● NEEDLE NOSE PLIERS (LONG TYPE) PAT.P.



NEEDLE NOSE PLIERS (LONG TYPE)

No.	Max Cutting Dia.		L	ℓ	W ₁	W ₂	T ₁	T ₂	▼g	⊞
	soft	hard								
PSL-200L	ø2.0	ø1.6	200	89	54	16	14	10	130	5




● NEEDLE NOSE PLIERS (SLIM TYPE) PAT.P.



NEEDLE NOSE PLIERS (SLIM TYPE)

No.	L	ℓ	W ₁	W ₂	T ₁	T ₂	▼g	⊞
PSL-175N	175	54	55	13.5	14.5	9	130	5

- No blade.



*Please check the merchandise inventory for a product that is marked by ⚠ before placing an order.