


# SPE-C Plastic Screw - Socket Head Cap Screws - PEEK



[WEB Selection Tool](#)  
 [WEB CAD Download](#)  
 [Chemical-proof](#)



● Material/Finish



	SPE-C
Main body	PEEK/Light brown
Heat Resistance Temperature*	180°C

\*This is the value for the plastic material. The maximum operating temperature of the product changes with performance conditions such as tightening torque.

**⚠ Precautions for Use**

Because a cumulative pitch difference is created when PEEK screws are manufactured, use these screws with nuts. If a nut is not used, use a 20 mm or less fit with female thread.

- PEEK is a thermoplastic super - engineering plastic with excellent physical and chemical properties.
- These screws have excellent chemical resistance. They are mostly unaffected by chemicals excluding concentrate sulfuric acid, concentrate nitric acid, and concentrate hydrofluoric acid.
- These screws have excellent heat resistance, water resistance, and high heat resistance strength.
- These screws have excellent abrasion, shock, and fatigue resistance.
- They have high incombustibility that meets V - 0 of UL 94.
- The properties and precautions of plastic screws → P.724

● Application

FPD production equipment, semiconductor devices, printed circuit board etching devices, metallic surface treatment equipment and facilities, chemical plants, transformers, electrical and electronic equipment, hot water pumps, and chemical pumps

Unit : mm

Part Number	M	L									D1	L1	B	Tension*1 Rupture Load (N)	Torsional*1 Torque (N·m)	Mass (g)
<b>SPE-M3-C</b>	M3	6	8	10	12	15	20	25			5.5	3	2.5	430	0.3	0.12 - 0.27
<b>SPE-M4-C</b>	M4	6	8	10	12	15	20	25	30		7	4	3	765	0.64	0.25 - 0.61
<b>SPE-M5-C</b>	M5	6	8	10	12	15	20	25	30		8.5	5	4	1230	1.28	0.37 - 0.93
<b>SPE-M6-C</b>	M6			10	12	15	20	25	30	40	10	6	5	1670	2.26	0.78 - 1.8
<b>SPE-M8-C</b>	M8					15	20	25	30	40	13	8	6	3090	5.98	2 - 3.5

\*1 Values in chart are for reference only. They are not guaranteed values. The recommendation torque is 50% of the torsional torque.

Part Number	Qty per pack*1
<b>SPE-M3-C</b>	20
<b>SPE-M4-C</b>	20
<b>SPE-M5-C</b>	10
<b>SPE-M6-C</b>	10
<b>SPE-M8-C</b>	5

\*1 The minimum order quantity is 1 piece. → P.794

● Related Products

**[SPE-N]** Plastic Hexagon Nut (PEEK) is available. → P.741



● Part number specification

## SPE - M5 - 20 - C

Product Code **1**      **2**      Product Code

Order in number of packs. The minimum order quantity is 1 piece. → P.794

<b>1</b> Individual Sales → P.794	<b>2</b> Cleanroom Wash & Packaging → P.792	<b>3</b> Screw Length Adjustment → P.796	<b>4</b> Vibration Resistant → P.795	<b>5</b> Modification process for captive use → P.791
Available / Add'l charge	Available / Add'l charge	Available / Add'l charge	Not Available	Please feel free to contact us

Special Screws  
 Vacuum Application  
 Low Profile, Small Head  
 High Performance S.S.  
 Titanium  
 Special Material  
 Chemical Resistance  
 Special Surface Treatment  
 Miniature  
 Captive/ Full Thread  
 Functional  
 Inch  
 Tamper Resistance  
 Hexabular Socket Head  
 Plugs  
 Plastic  
 Washers/ Lock Nuts