


●鋼からステンレス鋼そしてアルミまで、汎用コーティングドリルです。

This is general coated drills having jobbers length.



LIST 620P

オーダー方法

GTD 直径

直径2.0~6.9  
在庫品限り

切削条件 Drilling Condition A-236

単位 (Unit) : mm / 円 (¥)

直径 Dc	溝長 ℓ	全長 L	シャंक MT No.	在庫 Stock	参考価格 Price
2.0	29	105	1	□	-
2.1	29	110	1	□	-
2.2	33	110	1	□	-
2.3	33	110	1	□	-
2.4	35	110	1	□	-
2.5	35	110	1	□	-
2.6	37	115	1	□	-
2.7	37	115	1	□	-
2.8	39	115	1	□	-
2.9	42	115	1	□	-
3.0	42	115	1	□	-
3.1	42	122	1	□	-
3.2	42	122	1	□	-
3.3	45	122	1	□	-
3.4	45	122	1	□	-
3.5	45	122	1	□	-
3.6	48	128	1	□	-
3.7	48	128	1	□	-
3.8	48	128	1	□	-
3.9	51	128	1	□	-
4.0	54	135	1	□	-
4.1	54	135	1	□	-
4.2	54	135	1	□	-
4.3	54	135	1	□	-
4.4	56	135	1	□	-
4.5	56	135	1	□	-
4.6	56	135	1	□	-
4.7	59	140	1	□	-
4.8	59	140	1	□	-
4.9	62	140	1	□	-
5.0	62	140	1	□	-
5.1	62	145	1	□	-
5.2	64	145	1	□	-
5.3	64	145	1	□	-
5.4	64	145	1	□	-
5.5	64	145	1	□	-
5.6	67	148	1	□	-
5.7	67	148	1	□	-
5.8	67	148	1	□	-
5.9	67	148	1	□	-
6.0	70	148	1	□	-
6.1	70	152	1	□	-
6.2	70	152	1	□	-
6.3	70	152	1	□	-
6.4	73	152	1	□	-
6.5	73	152	1	□	-
6.6	73	155	1	□	-
6.7	73	155	1	□	-
6.8	73	155	1	□	-
6.9	73	155	1	□	-
7.0	67	148	1	●	5,440
7.1	67	148	1	□	-
7.2	67	148	1	□	-
7.3	67	148	1	□	-
7.4	67	148	1	□	-
7.5	67	148	1	●	5,690
7.6	73	154	1	□	-
7.7	73	154	1	□	-
7.8	73	154	1	□	-
7.9	73	154	1	□	-

直径 Dc	溝長 ℓ	全長 L	シャंक MT No.	在庫 Stock	参考価格 Price
8.0	73	154	1	●	5,730
8.1	73	154	1	□	-
8.2	73	154	1	□	-
8.3	73	154	1	□	-
8.4	73	154	1	□	-
8.5	73	154	1	●	5,850
8.6	78.5	159.5	1	□	-
8.7	78.5	159.5	1	□	-
8.8	78.5	159.5	1	□	-
8.9	78.5	159.5	1	□	-
9.0	78.5	159.5	1	●	6,010
9.1	78.5	159.5	1	□	-
9.2	78.5	159.5	1	□	-
9.3	78.5	159.5	1	□	-
9.4	78.5	159.5	1	□	-
9.5	78.5	159.5	1	●	6,150
9.6	84.5	165.5	1	□	-
9.7	84.5	165.5	1	□	-
9.8	84.5	165.5	1	□	-
9.9	84.5	165.5	1	□	-
10.0	84.5	165.5	1	●	6,530
10.1	84.5	165.5	1	□	-
10.2	84.5	165.5	1	□	-
10.3	84.5	165.5	1	□	-
10.4	84.5	165.5	1	□	-
10.5	84.5	165.5	1	●	6,700
10.6	91	172	1	□	-
10.7	91	172	1	□	-
10.8	91	172	1	□	-
10.9	91	172	1	□	-
11.0	91	172	1	●	7,270
11.1	91	172	1	□	-
11.2	91	172	1	□	-
11.3	91	172	1	□	-
11.4	91	172	1	□	-
11.5	91	172	1	●	7,640
11.6	91	172	1	□	-
11.7	91	172	1	□	-
11.8	91	172	1	□	-
11.9	98	179	1	□	-
12.0	98	179	1	●	7,750
12.1	98	179	1	□	-
12.2	98	179	1	□	-
12.3	98	179	1	□	-
12.4	98	179	1	□	-
12.5	98	179	1	●	8,120
12.6	98	179	1	□	-
12.7	98	179	1	□	-
12.8	98	179	1	□	-
12.9	98	179	1	□	-
13.0	98	179	1	●	8,150
13.1	98	179	1	□	-
13.2	98	179	1	□	-
13.3	104.5	185.5	1	□	-
13.4	104.5	185.5	1	□	-
13.5	104.5	185.5	1	●	8,960
13.6	104.5	185.5	1	□	-
13.7	104.5	185.5	1	□	-
13.8	104.5	185.5	1	□	-
13.9	104.5	185.5	1	□	-