


●もっとも広い用途で使用される汎用ドリルです。

This drill is applied for general purpose.



LIST 602

オーダ方法

TD 直径 (□商品: TD 直径 × シャンク)

切削条件 Drilling Condition ▶▶▶A-237

単位 (Unit): mm / 円 (¥)

直径 Dc	溝長 ℓ	全長 L	シャンク MT No.	在庫 Stock	参考価格 Price
7.0	75	155	1	●	2,410
7.1	78	158	1	●	2,750
7.2	78	158	1	●	2,750
7.3	78	158	1	●	2,750
7.4	78	158	1	●	2,750
7.5	78	158	1	●	2,450
7.6	82	162	1	●	2,800
7.7	82	162	1	●	2,800
7.8	82	162	1	●	2,800
7.9	82	162	1	●	2,800
8.0	82	162	1	●	2,510
8.1	85	168	1	●	2,970
8.2	85	168	1	●	2,970
8.3	85	168	1	●	2,970
8.4	85	168	1	●	2,970
8.5	85	168	1	●	2,660
8.6	88	172	1	●	3,160
8.7	88	172	1	●	3,160
8.8	88	172	1	●	3,160
8.9	88	172	1	●	3,160
9.0	88	172	1	●	2,800
9.1	92	175	1	●	3,340
9.2	92	175	1	●	3,340
9.3	92	175	1	●	3,340
9.4	92	175	1	●	3,340
9.5	92	175	1	●	3,000
9.6	95	178	1	●	3,480
9.7	95	178	1	●	3,480
9.8	95	178	1	●	3,480
9.9	95	178	1	●	3,480
10.0	95	178	1	●	3,120
10.1	98	182	1	●	3,550
10.2	98	182	1	●	3,550
10.3	98	182	1	●	3,550
10.4	98	182	1	●	3,550
10.5	98	182	1	●	3,190
10.6	102	185	1	●	3,720
10.7	102	185	1	●	3,720
10.8	102	185	1	●	3,720
10.9	102	185	1	●	3,720
11.0	102	185	1	●	3,390
11.1	105	188	1	●	3,820
11.2	105	188	1	●	3,820
11.3	105	188	1	●	3,820
11.4	105	188	1	●	3,820
11.5	105	188	1	●	3,470
11.6	108	192	1	●	4,070
11.7	108	192	1	●	4,070
11.8	108	192	1	●	4,070
11.9	108	192	1	●	4,070
12.0	108	192	1	●	3,720
12.1	112	195	1	●	4,280
12.2	112	195	1	●	4,280
12.3	112	195	1	●	4,280
12.4	112	195	1	●	4,280
12.5	112	195	1	●	3,890
12.6	115	198	1	●	4,400
12.7	115	198	1	●	4,400
12.8	115	198	1	●	4,400
12.9	115	198	1	●	4,400
13.0	115	198	1	●	4,010
13.1	118	202	1	●	4,610

直径 Dc	溝長 ℓ	全長 L	シャンク MT No.	在庫 Stock	参考価格 Price
13.2	118	202	1	●	4,610
13.3	118	202	1	●	4,610
13.4	118	202	1	●	4,610
13.5	118	202	1	●	4,210
13.6	122	205	1	●	4,760
13.7	122	205	1	●	4,760
13.8	122	205	1	●	4,760
13.9	122	205	1	●	4,760
14.0	122	205	1	●	4,360
14.1	122	222	2	●	5,350
14.2	122	222	2	●	5,350
14.3	122	222	2	●	5,350
14.4	122	222	2	●	5,350
14.5	122	222	2	●	4,880
14.6	125	225	2	●	5,490
14.7	125	225	2	●	5,490
14.8	125	225	2	●	5,490
14.9	125	225	2	●	5,490
15.0	125	225	2	●	5,000
15.1	128	228	2	●	5,770
15.2	128	228	2	●	5,770
15.3	128	228	2	●	5,770
15.4	128	228	2	●	5,770
15.5	128	228	2	●	5,250
15.6	130	230	2	●	6,020
15.7	130	230	2	●	6,020
15.8	130	230	2	●	6,020
15.9	130	230	2	●	6,020
16.0	130	230	2	●	5,480
16.1	132	232	2	●	6,550
16.2	132	232	2	●	6,550
16.3	132	232	2	●	6,550
16.4	132	232	2	●	6,550
16.5	132	232	2	●	5,940
16.6	135	235	2	●	6,910
16.7	135	235	2	●	6,910
16.8	135	235	2	●	6,910
16.9	135	235	2	●	6,910
17.0	135	235	2	●	6,270
17.1	140	240	2	●	7,220
17.2	140	240	2	●	7,220
17.3	140	240	2	●	7,220
17.4	140	240	2	●	7,220
17.5	140	240	2	●	6,560
17.6	140	240	2	●	7,630
17.7	140	240	2	●	7,630
17.8	140	240	2	●	7,630
17.9	140	240	2	●	7,630
18.0	140	240	2	●	6,950
18.1	145	245	2	●	7,840
18.2	145	245	2	●	7,840
18.3	145	245	2	●	7,840
18.4	145	245	2	●	7,840
18.5	145	245	2	●	7,130
18.6	145	245	2	●	8,230
18.7	145	245	2	●	8,230
18.8	145	245	2	●	8,230
18.9	145	245	2	●	8,230
19.0	145	245	2	●	7,470
19.1	150	250	2	●	8,680
19.2	150	250	2	●	8,680
19.3	150	250	2	●	8,680

総目次

Non Coat

穴深さ

~3D

~5D

~7D

~9D

深穴

ノス

ドリル

鉄骨

油穴付き

アルミ・

非鉄金属

ストレート

テーパ