


2AGE

AG ミル 2枚刃

AG-mill Two Flutes

●鋼からステンレス鋼、アルミまで高速・高効率加工
ができます。

This end mill is suitable for high-feed grooving of workpiece material from Carbon Steels and Stainless Steels to Aluminum.



LIST 6490

オーダ方法

2AGE 外形 *印商品のオーダ方法 2AGE 外形 × シャンク径

切削条件 Milling Condition ▶▶B-268

単位 (Unit): mm / 円 (¥)

外径 Dc	刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stack	参考価格 Price
1	2	50	6	●	3,210
1.1	2.5	50	6	●	4,150
1.2	2.5	50	6	●	4,150
1.3	3	50	6	●	4,150
1.4	3	50	6	●	4,150
1.5	3	50	6	●	3,000
1.6	3.5	50	6	●	3,880
1.7	3.5	50	6	●	3,880
1.8	4	50	6	●	3,880
1.9	4	50	6	●	3,880
2	4	50	6	●	2,840
2.1	4.5	50	6	●	3,680
2.2	4.5	50	6	●	3,680
2.3	5	50	6	●	3,680
2.4	5	50	6	●	3,680
2.5	5	50	6	●	2,800
2.6	5.5	50	6	●	3,620
2.7	5.5	50	6	●	3,620
2.8	6	50	6	●	3,620
2.9	6	50	6	●	3,620
3	6	50	6	●	2,460
3.1	6.5	50	6	●	3,190
3.2	6.5	50	6	●	3,190
3.3	7	50	6	●	3,190
3.4	7	50	6	●	3,190
3.5	8	60	8	●	2,460
3.6	8	60	8	●	3,190
3.7	8	60	8	●	3,190
3.8	8	60	8	●	3,190
3.9	8	60	8	●	3,190
4	8	60	8	●	2,460
4.1	9	60	8	●	3,190
4.2	9	60	8	●	3,190
4.3	10	60	8	●	3,190
4.4	10	60	8	●	3,190
4.5	10	60	8	●	2,460
4.6	10	60	8	●	3,190
4.7	10	60	8	●	3,190
4.8	10	60	8	●	3,190
4.9	10	60	8	●	3,190
5	10	60	8	●	2,460
5.1	12	60	8	●	3,190
5.2	12	60	8	●	3,190
5.3	12	60	8	●	3,190
5.4	12	60	8	●	3,190
5.5	12	60	8	●	2,460
5.6	12	60	8	●	3,190
5.7	12	60	8	●	3,190
5.8	12	60	8	●	3,190
5.9	12	60	8	●	3,190
6	12	60	8	●	2,460
6.1	14	65	8	●	3,190
6.2	14	65	8	●	3,190
6.3	14	65	8	●	3,190
6.4	14	65	8	●	3,190
6.5	14	65	10	●	2,690
6.6	14	65	10	●	3,480
6.7	14	65	10	●	3,480
6.8	14	65	10	●	3,480
6.9	14	65	10	●	3,480

外径 Dc	刃長 ℓ	全長 L	シャンク径 Ds	在庫 Stack	参考価格 Price
7	14	65	10	●	2,690
7.1	14	65	10	●	3,480
7.2	14	65	10	●	3,480
7.3	14	65	10	●	3,480
7.4	14	65	10	●	3,480
7.5	14	65	10	●	2,690
7.6	14	65	10	●	3,480
7.7	14	65	10	●	3,480
7.8	14	65	10	●	3,480
7.9	14	65	10	●	3,480
8	14	65	10	●	2,690
8.1	18	70	10	●	3,480
8.2	18	70	10	●	3,480
8.3	18	70	10	●	3,480
8.4	18	70	10	●	3,480
8.5	18	70	10	●	3,130
8.6	18	70	10	●	4,050
8.7	18	70	10	●	4,050
8.8	18	70	10	●	4,050
8.9	18	70	10	●	4,050
9	18	70	10	●	3,130
9.1	18	70	10	●	4,050
9.2	18	70	10	●	4,050
9.3	18	70	10	●	4,050
9.4	18	70	10	●	4,050
9.5	18	70	10	●	3,130
9.6	18	70	10	●	4,050
9.7	18	70	10	●	4,050
9.8	18	70	10	●	4,050
9.9	18	70	10	●	4,050
10	18	70	10	●	3,130
10.1	22	80	12	●	5,420
10.2	22	80	12	●	5,420
10.3	22	80	12	●	5,420
10.4	22	80	12	●	5,420
10.5	22	80	12	●	5,420
10.6	22	80	12	●	5,420
10.7	22	80	12	●	5,420
10.8	22	80	12	●	5,420
10.9	22	80	12	●	5,420
11	22	80	12	●	4,030
11.1	22	80	12	●	5,420
11.2	22	80	12	●	5,420
11.3	22	80	12	●	5,420
11.4	22	80	12	●	5,420
11.5	22	80	12	●	5,420
11.6	22	80	12	●	5,420
11.7	22	80	12	●	5,420
11.8	22	80	12	●	5,420
11.9	22	80	12	●	5,420
12	22	80	12	●	4,030
12.1	26	90	16	●	6,720
12.2	26	90	16	●	6,720
12.3	26	90	16	●	6,720
12.4	26	90	16	●	6,720
12.5	26	90	16	●	6,720
12.6	26	90	16	●	6,720
12.7	26	90	16	●	6,720
12.8	26	90	16	●	6,720
12.9	26	90	16	●	6,720