


● OPEN END WRENCH



OPEN END WRENCH										mm
No.	S ₁ ×S ₂	D ₁	D ₂	T ₁	T ₂	L	▽g	⊕		
S2-05507	5.5×7	12.5	15.5	3.5	3.5	102	15	5		
-0607	6×7	13	15.5	3.5	3.5	102	15	5		
-0608	6×8	13	17.5	4	4	107	18	5		
-0708	7×8	15.5	17.5	4	4	112	20	5		
-0809	8×9	17.5	19.5	4.5	4.5	118	30	5		
-0810	8×10	17.5	21.5	4.5	4.5	122	40	5		
-1011	10×11	21.5	23.5	5	5	133	45	5		
-1012	10×12	21.5	25.5	5.5	5.5	138	60	5		
-1013	10×13	21.5	27.5	6	6	143	60	5		
-1014	10×14	21.5	29.5	6.5	6.5	148	65	5		
-1113	11×13	23.5	27.5	6	6	147	65	5		
-1214	12×14	25.5	29.5	6.5	6.5	157	75	5		
-1315	13×15	27.5	31.5	7	7	164	90	5		
-1317	13×17	27.5	36	7	7	168	100	5		
-1417	14×17	29.5	36	7	7	173	105	5		
-1618	16×18	33.5	38	8	8	188	135	5		
-1719	17×19	36	40	7.5	7.5	195	145	5		
-1721	17×21	36	44	8	8	203	170	5		
-1921	19×21	40	44	8	8	218	195	5		
-1922	19×22	40	46	8.5	8.5	223	205	5		
-2022	20×22	42	46	8.5	8.5	228	215	5		
-2123	21×23	44	48	8.5	8.5	233	240	5		
-2126	21×26	44	54	8.5	8.5	238	260	5		
-2224	22×24	46	50	9	9	244	260	5		
-2326	23×26	48	54	9	9	248	300	5		
-2427	24×27	50	55.5	9	9	253	320	5		
-2528	25×28	52	57.5	9.5	9.5	263	365	5		
-2632	26×32	54	65.5	10.5	10.5	273	460	5		
-2730	27×30	55.5	61.5	10	10	274	430	5		
-2732	27×32	55.5	65.5	10.5	10.5	284	480	5		
-2932	29×32	60	65.5	10.5	10.5	288	510	5		
-3032	30×32	61.5	65.5	10.5	10.5	294	525	5		
-3236	32×36	65.5	74	12	12	318	710	5		
-3538	35×38	72	78	13.5	13.5	334	905	5		
-3638	36×38	74	78	13.5	13.5	354	945	5		
-4146	41×46	84	94	14	14	399	1315	5		

OPEN END WRENCH										in
No.	S ₁ ×S ₂	D ₁	D ₂	T ₁	T ₂	L	▽g	⊕		
S2-1/4x5/16	6.3×7.9	13	17.5	4	4	107	18	5		
-5/16x3/8	7.9×9.5	17.5	21.5	4.5	4.5	122	40	5		
-3/8x7/16	9.5×11.1	21.5	23.5	5	5	133	45	5		
-13/32x1/2	10.3×12.7	21.5	27.5	6	6	143	60	5		
-7/16x1/2	11.1×12.7	23.5	27.5	6	6	147	65	5		
-1/2x9/16	12.7×14.2	27.5	29.5	6.5	6.5	160	74	5		
-9/16x5/8	14.2×15.8	29.5	33.5	7	7	169	97	5		
-19/32x11/16	15×17.4	31.5	36	7	7	175	106	5		
-5/8x11/16	15.8×17.4	33.5	36	7	7	177	110	5		
-5/8x3/4	15.8×19	33.5	40	7.5	7.5	192	133	5		
-11/16x3/4	17.4×19	36	40	7.5	7.5	195	145	5		
-3/4x25/32	19×19.8	40	42	8	8	216	177	5		
-3/4x13/16	19×20.6	40	44	8	8	218	195	5		
-25/4x7/8	19.8×22.2	42	46	8.5	8.5	228	215	5		
-13/16x7/8	20.6×22.2	44	46	8.5	8.5	231	224	5		
-15/16x1	23.8×25.4	50	52	9	9	249	300	5		
-1-x1-1/16	25.4×26.9	52	55.5	9	9	256	327	5		
-1-1/8x1-1/4	28.5×31.7	60	65.5	10.5	10.5	288	510	5		

● SLIM TYPE OPEN END WRENCH



SLIM TYPE OPEN END WRENCH (S20)								mm
No.	S ₁ ×S ₂	D ₁	D ₂	T	L	▽g	⊕	
S20-10×12	10×12	21	26	4	210	64	5	
-12×10	12×10	26	21	4	210	64	5	
-12×14	12×14	26	30	4	215	75	5	
-14×12	14×12	30	26	4	215	75	5	
-17×19	17×19	36	40	4.5	235	120	5	
-19×17	19×17	40	36	4.5	235	120	5	

SLIM TYPE OPEN END WRENCH SET (6pcs.)				mm
No. S206	▽g	544	⊕	1
Slim Type Open End Wrench (mm) S20-10×12, 12×10, 12×14, 14×12, 17×19, 19×17				

- Set of each 2 pcs. of same size combination with different angles.
- Fit to use in small spaces for tightening/loosening double nuts (Fig.1)

