



● COMBINATION WRENCH



COMBINATION WRENCH									mm
No.	S*	D ₁	D ₂	T ₁	T ₂	L	▽g	⊞	
MS2- 032	3.2	8	7.5	3	3	75	6	5	
- 04	4	9	8.5	3	4	80	8	5	
- 045	4.5	10	9	3	4	85	10	5	
- 05	5	11	9.5	3	4.5	90	11	5	
- 055	5.5	12.5	10	3	4.5	96	13	5	
- 06	6	13	10.5	3	4.5	96	14	5	
- 07	7	15.5	12	3.5	5	111	20	5	
- 08	8	17.5	13	4	5.5	126	28	5	
- 09	9	19.5	14.5	4.5	6	136	36	5	
- 10	10	21.5	16	4.5	6.5	151	42	5	
- 11	11	23.5	17	5	7	161	55	5	
- 12	12	25.5	18	5.5	7.5	170	65	5	
- 13	13	27.5	19	6	8.5	188	85	5	
- 14	14	29.5	20.5	6	9.5	190	98	5	
- 15	15	31.5	22.5	7	10	200	119	5	
- 16	16	33.5	23.5	7	10.5	215	134	5	
- 17	17	36	25	7	10.5	225	153	5	
- 18	18	38	26.5	8	11.5	241	184	5	
- 19	19	40	27.5	7.5	12	256	205	5	
- 20	20	42	29.5	8	12	271	234	5	
- 21	21	44	30.5	8	13	289	267	5	
- 22	22	46	32	8.5	13.5	304	305	5	
- 23	23	48	33.5	8.5	14.5	311	331	5	
- 24	24	50	35	9	15	337	380	5	
- 25	25	52	36	9	15.5	351	423	5	
- 26	26	54	37.5	9	16	371	466	5	
- 27	27	55.5	39	9	16.5	381	502	5	
- 28	28	57.5	40.5	9.5	17	401	561	5	
- 29	29	60	43.5	10	18	421	650	1	
- 30	30	61.5	43.5	10	18	446	687	1	
- 31	31	63.5	45.5	10.5	18	462	790	1	
- 32	32	65.5	46.5	10.5	18	471	836	1	
- 33	33	67.5	47.5	11	20	477	904	1	
- 34	34	69.5	52	11	21	480	1030	1	
- 35	35	72	52	12	21	481	1070	1	
- 36	36	74	52	12	21	501	1155	1	
- 38	38	78	54.5	13.5	22	521	1382	1	
- 41	41	84	59	14	24.5	542	1680	1	
- 46	46	94	66	14	26	562	2142	1	

* 5mm and below the offset side is the hexagonal diameter. **POWERFIT** (Except the following from 5mm)

● COMBINATION WRENCH



COMBINATION WRENCH									in
No.	S*	D ₁	D ₂	T ₁	T ₂	L	▽g	⊞	
MS2-1/8	3.1	8	7.5	3	3	75	6	5	
-5/32	3.9	9	8.5	3	4	80	8	5	
-3/16	4.7	10	9	3	4	85	10	5	
-13/64	5.1	11	9.5	3	4.5	90	11	5	
-7/32	5.5	12.5	10	3	4.5	96	13	5	
-15/64	5.9	13	10.5	3	4.5	96	14	5	
-1/4	6.3	13	10.5	3	4.5	96	14	5	
-9/32	7.1	15.5	12	3.5	5	111	20	5	
-5/16	7.9	17.5	13	4	5.5	126	28	5	
-11/32	8.7	19.5	14.5	4.5	6	136	36	5	
-3/8	9.5	21.5	16	4.5	6.5	151	42	5	
-7/16	11.1	23.5	17	5	7	161	55	5	
-1/2	12.7	27.5	19	6	8.5	188	85	5	
-9/16	14.2	29.5	20.5	6	9.5	190	98	5	
-19/32	15	31.5	22.5	7	10	200	119	5	
-5/8	15.8	33.5	23.5	7	10.5	215	134	5	
-11/16	17.4	36	25	7	10.5	225	153	5	
-3/4	19	40	27.5	7.5	12	256	205	5	
-25/32	19.8	42	29.5	8	12	271	234	5	
-13/16	20.6	44	30.5	8	13	289	267	5	
-7/8	22.2	46	32	8.5	13.5	304	305	5	
-15/16	23.8	50	35	9	15	337	380	5	
-1	25.4	52	36	9	15.5	351	423	5	
-1-1/16	26.9	55.5	39	9	16.5	381	502	5	
-1-1/8	28.5	60	43.5	10	18	421	650	5	
-1-3/16	30.1	61.5	43.5	10	18	446	687	5	
-1-1/4	31.7	65.5	46.5	10.5	18	471	836	5	
-1-5/16	33.3	67.5	47.5	11	20	477	904	5	
-1-3/8	34.9	72	52	12	21	481	1070	1	
-1-7/16	36.5	74	52	12	21	501	1155	1	
-1-1/2	38.1	78	54.5	13.5	22	521	1382	1	

* 13/64in and below the offset side is the hexagonal diameter.