

FEELER GAUGE (WIDE TYPE)

Essential for assembly and adjustment



12.7mm wide (normal) type ▶
Feeler Gauge
P86
~87

Multiple sizes in one product ▶
Thickness Gauge
P88
~90

Rust prevention ▶
Zerust Film for Steel
P380



USE

- For measurement of gap width
- For assemble or adjustment of automotive engine components or other machinery

MATERIAL

- Stainless steel (SUS304) [RoHS Compliant]

FEATURES

- Can be cut to necessary size
- Convenient cardboard storage box
- Made of stainless steel, rust resistant

SPECIFICATIONS


- Leaf Length: 1m
- Case Size: 80×88×40mm (30mm width)
90×90×60mm (50mm width)



Can be cut to necessary size

● DIMENSIONS

Units: mm



Order No.	Model No.	Leaf Width (W) (mm)	Thickness (t) (mm)	Thickness Accuracy (t) (mm)
007391	SFG30-005-1	30	0.005	±0.0005
007392	SFG30-01-1		0.01	±0.001
007393	SFG30-02-1		0.02	±0.002
007394	SFG30-03-1		0.03	±0.003
007395	SFG30-04-1		0.04	±0.004
007396	SFG30-05-1		0.05	±0.005
007397	SFG30-06-1		0.06	±0.006
007398	SFG30-08-1		0.08	±0.008
007399	SFG30-10-1		0.1	±0.01
007400	SFG50-005-1		50	0.005
007401	SFG50-01-1	0.01		±0.001
007402	SFG50-02-1	0.02		±0.002
007403	SFG50-03-1	0.03		±0.003
007404	SFG50-04-1	0.04		±0.004
007405	SFG50-05-1	0.05		±0.005
007406	SFG50-06-1	0.06		±0.006
007407	SFG50-08-1	0.08		±0.008
007408	SFG50-10-1	0.1		±0.01

BLOCK GAUGE

PIN GAUGE

PIN VISE

PIN GAUGE ACCESSORIES

RING GAUGE

PLUG GAUGE

LIMIT GAUGE

THICKNESS GAUGE

TAPER GAUGE

WELDING GAUGE

OTHER GAUGES

FEELER GAUGE (SFG SERIES)

Essential for assembly and fitting work



USE

- For measurement of gap width
- For assemble or adjustment of automotive engine components or other machinery

MATERIAL

- Leaf thickness: 0.01mm Stainless steel SUS301H
0.005·0.02~0.10mm Stainless steel SUS304H

FEATURES

- Can be cut to necessary size

SPECIFICATIONS

- Leaf width: 12.7mm ● Leaf hardness: HV300 and above ● Case Size: 77×77×22mm
- ※ White powder remains on the surface of the product is antirust agent



Wide width type ▶
Feeler Gauge (Wide type)
P86

Multiple sizes in one product ▶
Thickness Gauge
P88
~90

Rust prevention ▶
Zerust Film for Steel
P380

Order No.	Model No.	Size (mm)	Leaf Width (mm)	Leaf Length (m)	Accuracy (mm)	Weight (including case)	
007245	SFG-005-1	0.005×1m	0.005	1	±0.004	34g	
007251	SFG-01-1	0.01 ×1m	0.01			34g	
007252	SFG-02-1	0.02 ×1m	0.02			35g	
007381	SFG-03-1	0.03 ×1m	0.03			36g	
007382	SFG-04-1	0.04 ×1m	0.04			37g	
007383	SFG-05-1	0.05 ×1m	0.05			38g	
007384	SFG-06-1	0.06 ×1m	0.06			39g	
007385	SFG-07-1	0.07 ×1m	0.07			40g	
007386	SFG-08-1	0.08 ×1m	0.08			41g	
007387	SFG-09-1	0.09 ×1m	0.09			42g	
007388	SFG-10-1	0.10 ×1m	0.10	±0.006	43g		
007421	SFG-01-3	0.01 ×3m	0.01	3	±0.004	36g	
007422	SFG-02-3	0.02 ×3m	0.02			39g	
007423	SFG-03-3	0.03 ×3m	0.03			42g	
007424	SFG-04-3	0.04 ×3m	0.04			±0.005	45g
007425	SFG-05-3	0.05 ×3m	0.05			48g	

Order No.	Model No.	Size (mm)	Leaf Width (mm)	Leaf Length (m)	Accuracy (mm)	Weight (including case)	
007426	SFG-06-3	0.06×3m	0.06	3	±0.005	51g	
007427	SFG-07-3	0.07×3m	0.07			54g	
007428	SFG-08-3	0.08×3m	0.08			57g	
007429	SFG-09-3	0.09×3m	0.09			60g	
007430	SFG-10-3	0.10×3m	0.10			±0.006	63g
007411	SFG-01-5	0.01×5m	0.01			5	±0.004
007412	SFG-02-5	0.02×5m	0.02	43g			
007413	SFG-03-5	0.03×5m	0.03	48g			
007414	SFG-04-5	0.04×5m	0.04	53g			
007415	SFG-05-5	0.05×5m	0.05	58g			
007416	SFG-06-5	0.06×5m	0.06	±0.005	63g		
007417	SFG-07-5	0.07×5m	0.07	68g			
007418	SFG-08-5	0.08×5m	0.08	73g			
007419	SFG-09-5	0.09×5m	0.09	78g			
007420	SFG-10-5	0.10×5m	0.10	±0.006	83g		