


Tee




●Millimeter size type (Group 4)

Product number	Applicable tube outer diameter- inner diameter (mm)	T Thread size (R)	L1 (mm)	L2 (mm)	L4 (mm)	L5 (mm)	A (mm)	S (mm)	F Tube insertion length (mm)	H1 Width across flat (mm)	H2 Width across flat (mm)	d1 (mm)	d2 Min. inner diameter (mm)	Effective cross-sectional area (mm ²)	Weight (g)
T4N6×4-PT1/8-S	6×4	R1/8	20.5	18.5	25.4	41.0	11.0	4.6	15	10.0	12.0	5.0	2.7	4.5	30.0
T4N6×4-PT1/4-S	6×4	R1/4	23.0	22.0	28.9	46.0	12.0	4.6	15	12.0	12.0	7.0	2.7	4.5	43.0
T4N8×5-PT1/8-S	8×5	R1/8	22.9	21.0	29.1	45.8	11.0	4.6	16	12.0	14.0	5.0	3.7	9.0	43.0
T4N8×5-PT1/4-S	8×5	R1/4	22.9	22.0	30.1	45.8	12.0	4.6	16	12.0	14.0	7.0	3.7	9.0	45.0
T4N8×6-PT1/8-S	8×6	R1/8	22.9	21.0	29.1	45.8	11.0	4.6	16	12.0	14.0	5.0	4.7	14.0	42.0
T4N8×6-PT1/4-S	8×6	R1/4	22.9	22.0	30.1	45.8	12.0	4.6	16	12.0	14.0	7.0	4.7	15.0	44.0
T4N10×6.5-PT1/4-S	10×6.5	R1/4	27.1	25.0	34.8	54.2	12.0	4.2	17	14.0	17.0	7.0	5.2	18.0	73.0
T4N10×6.5-PT3/8-S	10×6.5	R3/8	28.1	26.0	35.8	56.2	13.0	4.2	17	14.0	17.0	9.0	5.2	18.0	78.0
T4N10×8-PT1/4-S	10×8	R1/4	27.1	25.0	34.8	54.2	12.0	4.2	17	14.0	17.0	7.0	6.7	25.0	69.0
T4N10×8-PT3/8-S	10×8	R3/8	27.1	26.0	35.8	54.2	13.0	4.2	17	14.0	17.0	9.0	6.7	25.0	75.0
T4N12×8-PT3/8-S	12×8	R3/8	27.6	25.0	36.0	55.3	13.0	4.2	18	14.0	19.0	9.0	6.6	25.0	82.0
T4N12×9-PT3/8-S	12×9	R3/8	27.6	26.0	37.0	55.3	13.0	4.8	18	14.0	19.0	9.0	7.6	33.0	82.0

●Inch size type (Group 1)

Product number	Applicable tube outer diameter (inch)	T Thread size (R)	L1 (mm)	L2 (mm)	L4 (mm)	L5 (mm)	A (mm)	S (mm)	F Tube insertion length (mm)	H1 Width across flat (mm)	H2 Width across flat (mm)	d1 (mm)	d2 Min. inner diameter (mm)	Effective cross-sectional area (mm ²)	Weight (g)
T1N1/4-PT1/8-S	1/4	R1/8	20.5	18.5	25.4	41.1	11.0	4.6	15	10.0	12.0	5.0	3.4	8.0	29.0
T1N1/4-PT1/4-S	1/4	R1/4	23.0	22.0	28.9	46.1	12.0	4.6	15	12.0	12.0	7.0	3.4	8.0	42.0
T1N3/8-PT1/4-S	3/8	R1/4	23.7	22.0	31.8	47.4	12.0	4.6	17	12.0	17.0	7.0	5.7	19.0	55.0

Service tee



●Millimeter size type (Group 4)

Product number	Applicable tube outer diameter- inner diameter (mm)	T Thread size (R)	L1 (mm)	L2 (mm)	L6 (mm)	L7 (mm)	L8 (mm)	A (mm)	S (mm)	F Tube insertion length (mm)	H1 Width across flat (mm)	H2 Width across flat (mm)	d1 (mm)	d2 Min. inner diameter (mm)	Effective cross-sectional area (mm ²)	Weight (g)
ST4N6×4-PT1/8-S	6×4	R1/8	20.5	18.5	20.5	39.0	27.4	11.0	4.6	15	10.0	12.0	5.0	2.7	4.5	41.0
ST4N6×4-PT1/4-S	6×4	R1/4	23.0	22.0	23.0	45.0	29.9	12.0	4.6	15	12.0	12.0	7.0	2.7	4.5	30.0
ST4N8×5-PT1/8-S	8×5	R1/8	22.9	21.0	22.9	43.9	31.0	11.0	4.6	16	12.0	14.0	5.0	3.7	9.0	43.0
ST4N8×5-PT1/4-S	8×5	R1/4	22.9	22.0	22.9	44.9	31.0	12.0	4.6	16	12.0	14.0	7.0	3.7	9.0	43.0
ST4N8×6-PT1/8-S	8×6	R1/8	22.9	21.0	22.9	43.9	31.0	11.0	4.6	16	12.0	14.0	5.0	4.7	14.0	45.0
ST4N8×6-PT1/4-S	8×6	R1/4	22.9	22.0	22.9	44.9	31.0	12.0	4.6	16	12.0	14.0	7.0	4.7	15.0	46.0
ST4N10×6.5-PT1/4-S	10×6.5	R1/4	27.1	25.0	27.1	52.1	36.9	12.0	4.2	17	14.0	17.0	7.0	5.2	18.0	72.0
ST4N10×6.5-PT3/8-S	10×6.5	R3/8	27.1	26.0	27.1	53.1	36.9	13.0	4.2	17	14.0	17.0	9.0	5.2	18.0	70.0
ST4N10×8-PT1/4-S	10×8	R1/4	27.1	25.0	27.1	52.1	36.9	12.0	4.2	17	14.0	17.0	7.0	6.7	25.0	76.0
ST4N10×8-PT3/8-S	10×8	R3/8	27.1	26.0	27.1	53.1	36.9	13.0	4.2	17	14.0	17.0	9.0	6.7	25.0	113.0
ST4N12×8-PT3/8-S	12×8	R3/8	27.6	26.0	27.6	53.6	38.6	13.0	4.8	18	14.0	19.0	9.0	6.6	25.0	81.0
ST4N12×9-PT3/8-S	12×9	R3/8	27.6	26.0	27.6	53.6	38.6	13.0	4.8	18	14.0	19.0	9.0	7.6	33.0	130.0

●Inch size type (Group 1)

Product number	Applicable tube outer diameter (inch)	T Thread size (R)	L1 (mm)	L2 (mm)	L6 (mm)	L7 (mm)	L8 (mm)	A (mm)	S (mm)	F Tube insertion length (mm)	H1 Width across flat (mm)	H2 Width across flat (mm)	d1 (mm)	d2 Min. inner diameter (mm)	Effective cross-sectional area (mm ²)	Weight (g)
ST1N1/4-PT1/8-S	1/4	R1/8	20.5	18.5	20.5	39.0	27.5	11.0	4.6	15	10.0	12.0	5.0	3.4	8.0	29.0

Tube

Clean tube

Processed tube

PushOne fitting

QuickSeal fitting

Clean fitting/ Chemifit

Bamboo-shoot fitting

Control switch/ Detachable series

Jig/Tool/ Accessory

Technical information

Reference