


G-LIST No DW1016

極小径UVMドリル5Dタイプ

CARBIDE ULTRA SMALL SIZE UVM DRILL 5D TYPE

UVM-DRL-5D




info



●マークの説明はP.2をご覧ください。
See page 2 for explanation of icons.

今までにない領域の極小径穴あけ加工を実現！ 最小径φ0.02！
Ultra small size ever. The smallest size 0.02mm.



単位:mm Unit:mm

ツールNo. EDP No.	直径×シャンク径 Dc × Ds	溝長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	重量 Weight	標準価格 (Yen)	
8589002	0.02 × 3	0.12	38	3	C	9	29,400	
8589003	0.03 × 3	0.18				9	25,600	
8589004	0.04 × 3	0.24				9	21,400	
8589005	0.05 × 3	0.3				9	19,700	
	0.06 × 3	0.36				□	—	
	0.07 × 3	0.42				□	—	
8589008	0.08 × 3	0.48				C	9	12,500
	0.09 × 3	0.54				□	—	

ツールNo. EDP No.	直径×シャンク径 Dc × Ds	溝長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	重量 Weight	標準価格 (Yen)	
8589052	0.02 × 3.175	0.12	38	3.175	C	9	29,400	
8589053	0.03 × 3.175	0.18				9	25,600	
8589054	0.04 × 3.175	0.24				9	21,400	
8589055	0.05 × 3.175	0.3				9	19,700	
*	0.06 × 3.175	0.36				*	—	
*	0.07 × 3.175	0.42				*	—	
8589058	0.08 × 3.175	0.48				C	9	12,500
*	0.09 × 3.175	0.54				*	—	

* = 受注品
1. 切削油剤はP.870をご参照下さい。


* = Special order products.
1. Cutting fluid : Please refer to P.870.

G-LIST No DW1017


極小径UVMドリル10Dタイプ

CARBIDE ULTRA SMALL SIZE UVM DRILL 10D TYPE

UVM-DRL-10D




info



●マークの説明はP.2をご覧ください。
See page 2 for explanation of icons.

今までにない領域の極小径穴あけ加工を実現！ 最小径φ0.02！
Ultra small size ever. The smallest size 0.02mm.



単位:mm Unit:mm

ツールNo. EDP No.	直径×シャンク径 Dc × Ds	溝長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	重量 Weight	標準価格 (Yen)	
8589102	0.02 × 3	0.22	38	3	C	9	34,300	
8589103	0.03 × 3	0.33				9	30,000	
8589104	0.04 × 3	0.44				9	25,400	
8589105	0.05 × 3	0.55				9	23,100	
	0.06 × 3	0.66				□	—	
	0.07 × 3	0.77				□	—	
8589108	0.08 × 3	0.88				C	9	14,700
	0.09 × 3	0.99				□	—	

ツールNo. EDP No.	直径×シャンク径 Dc × Ds	溝長 ℓ	全長 L	シャンク径 Ds	在庫 Stock	重量 Weight	標準価格 (Yen)	
8589152	0.02 × 3.175	0.22	38	3.175	C	9	34,300	
8589153	0.03 × 3.175	0.33				9	30,000	
8589154	0.04 × 3.175	0.44				9	25,400	
8589155	0.05 × 3.175	0.55				9	23,100	
*	0.06 × 3.175	0.66				*	—	
*	0.07 × 3.175	0.77				*	—	
8589158	0.08 × 3.175	0.88				C	9	14,700
*	0.09 × 3.175	0.99				*	—	

* = 受注品
1. 切削油剤はP.870をご参照下さい。

* = Special order products.
1. Cutting fluid : Please refer to P.870.

低炭素鋼	中炭素鋼	高炭素鋼	合金鋼	調質鋼	焼入鋼	ステンレス鋼	工具鋼	鋳鉄	ダクタイル鋳鉄	銅合金	アルミ展伸材	アルミ合金鋳物	チタン合金	マナポルセラミック			
Low Carbon Steel	Medium Carbon Steel	High Carbon Steel	Alloy Steel	Hardened Steel	Quenched and Tempered Steel	Stainless Steel	Tool Steel	Cast Iron	Ductile Cast Iron	Copper Alloy	Aluminum	Aluminum Alloy Casting	Titanium Alloy	Machinable Ceramics			
C~0.25%	0.25~0.45%	C0.45%~	SCM	~35 HRC	35~45 HRC	45~50 HRC	50~62 HRC	62~70 HRC	SUS	SKD SKS	FC	FCD	Cu	AL	AC		
UVM-DRL-5D																	
					○	○	○		○				○	○	○	○	
UVM-DRL-10D																	
					○	○	○		○				○	○	○	○	

A, B, C, D=標準在庫品 A, B, C, D=Standard stock item.
□=特定代理店在庫品 □=Stocked by specific distributors. Contact us for price & availability.

SPECIFICATION CHART
形状寸法表
DRILLS
超硬ドリル
CARBIDE DRILLS