


G-LIST No TH1169

Vコーティング粉末ハイス V COATED・POWDER METALLURGY H.S.S

VP-SFT



●マークの説明はP.2をご覧ください。
See page 2 for explanation of icons.

ツールNo. EDP NO.	呼び Thread Size	精度 Grade	食付 TAP Limit	全長 Lc	ねじ長 L	首下長 Ln	シャンク径 Ds	溝数 Flutes	突出し センチ External Centre	在庫 Stock	重量 Weight	標準価格 (Yen)
8319269	M 3 x 0.5			46	3.5	19	4	—	—		4	2,620
8319283	M 4 x 0.7	STD	OH2	52	4.9	21	5	有	有		7	2,570
8319290	M 5 x 0.8			60	5.6	24	5.5	3	有	B	10	2,590
8319297	M 6 x 1			62	7	29	6	有	有		12	2,690
8319307	M 8 x 1.25	STD	OH3	70	8.5	37	6.2	—	—		17	3,510

■ 突き出しセンチ長さ・シャンク四角部寸法 Lk, KはP.890をご覧ください。

1. 精度欄 〇 は2級めねじ相当適応のタップ推奨精度です。(P.706参照)
2. 2002年7月生産以前のもので M3以下は突き出しセンチとなります。
3. タップ精度はめねじ精度を保証するものではありません。
4. 切削油剤、ペーストはP.868をご参照下さい。

※送りの不安定な機械で使用しますと、めねじ拡大トラブルが発生する場合がありますのでご注意ください。

単位:mm Unit:mm

ツールNo. EDP NO.	呼び Thread Size	精度 Grade	食付 TAP Limit	全長 Lc	ねじ長 L	首下長 Ln	シャンク径 Ds	溝数 Flutes	突出し センチ External Centre	在庫 Stock	重量 Weight	標準価格 (Yen)
8319317	M10 x 1.5			75	10.5	41	7	—	—		25	4,220
8319321	M10 x 1.25			75	10.5	41	7	—	—		25	4,220
8319330	M12 x 1.75	STD	OH3	82	12	48	8.5	3	—	B	38	5,490
8319334	M12 x 1.5			82	12	48	8.5	—	—		38	5,490
8319337	M12 x 1.25			82	12	48	8.5	—	—		38	5,490

■ Please see page 890 for length of external centre and shank square length Lk and width K.

1. The recommended TAP Limit corresponds to JIS class 2 internal thread standard. (see page 706)
2. Taps of M3 or less produced before July 2002 have external center.
3. TAP Limit does not guarantee thread limit for the internal thread after tapping.
4. Cutting fluid and Paste : Please refer to P.868.

※ Stable feed control machines are recommended to avoid over size tapping.



商品シリーズ

Parts & Supply series

圧縮空気を利用した産業用
バキュームクリーナー

※詳細は▶P.860を参照ください。
Please refer P.860 for the details



低炭素鋼	中炭素鋼	高炭素鋼	合金鋼	調質鋼	ステンレス鋼	工具鋼	鋳鋼	鋳鉄	ダクタイル鋳鉄	銅	黄銅	黄銅鋳物	青銅	アルミ圧延材	アルミ合金鋳物	マグネシウム合金鋳物	亜鉛合金鋳物	チタン合金	Ni基合金	熱硬化性プラスチック	熱可塑性プラスチック
Low Carbon Steel	Medium Carbon Steel	High Carbon Steel	Alloy Steel	Hardened Steel	Stainless Steel	Tool Steel	Cast Steel	Cast Iron	Ductile Cast Iron	Copper	Brass	Brass Casting	Bronze	Aluminum Rolled	Aluminum Alloy Casting	Magnesium Alloy Casting	Zinc Alloy Casting	Titanium Alloy	Nickel Alloy	Thermo Setting Plastic	Thermo Plastic
C ~0.25%	C0.25% ~0.45%	C 0.45% ~	SCM	25~45 HRC	45~55 HRC	50~60 HRC	SUS	SKD	SC	FC	FCD	Cu	Bs	BsC	PB	AL	AC,ADC	MC	ZDC		
		○	○	○																	

A, B, C, D=標準在庫品 A, B, C, D=Standard stock item.

□=特定代理店在庫品 □=Stocked by specific distributors. Contact us for price & availability.