


Square flanged units cast housing Set screw type



Press steel dust cover type (Open end)
S-UCF...D1

Cast dust cover type (Open end)
C-UCF...D1

Shaft dia.	Unit number ¹⁾	Nominal dimensions									Bolt size	Bearing number
		mm					inch					
		<i>L</i>	<i>J</i>	<i>A</i> ₂	<i>A</i> ₁	<i>A</i>	<i>N</i>	<i>A</i> ₀	<i>B</i>	<i>S</i>		
12 1½	UCF201D1 UCF201-008D1	86 3⅜	64 2⅜	15 19/32	11 7/16	25.5 1	12 15/32	33.3 1⅝	31 1.2205	12.7 0.500	M10 ⅜	UC201D1 UC201-008D1
15 9/16 5/8	UCF202D1 UCF202-009D1 UCF202-010D1	86 3⅜	64 2⅜	15 19/32	11 7/16	25.5 1	12 15/32	33.3 1⅝	31 1.2205	12.7 0.500	M10 ⅜	UC202D1 UC202-009D1 UC202-010D1
17 1⅞	UCF203D1 UCF203-011D1	86 3⅜	64 2⅜	15 19/32	11 7/16	25.5 1	12 15/32	33.3 1⅝	31 1.2205	12.7 0.500	M10 ⅜	UC203D1 UC203-011D1
20 ¾	UCF204D1 UCF204-012D1	86 3⅜	64 2⅜	15 19/32	11 7/16	25.5 1	12 15/32	33.3 1⅝	31 1.2205	12.7 0.500	M10 ⅜	UC204D1 UC204-012D1
25 1⅜ 7/8 1⅝ 1	UCF205D1 UCF205-013D1 UCF205-014D1 UCF205-015D1 UCF205-100D1	95 3¾	70 2¾	16 5/8	13 ½	27 1⅞	12 15/32	35.8 1⅝	34.1 1.3425	14.3 0.563	M10 ⅜	UC205D1 UC205-013D1 UC205-014D1 UC205-015D1 UC205-100D1
30 1⅞ 1⅞ 1⅜ 1¼	UCF206D1 UCF206-101D1 UCF206-102D1 UCF206-103D1 UCF206-104D1	108 4¼	83 3⅞	18 45/64	13 ½	31 1⅞	12 15/32	40.2 1⅝	38.1 1.5000	15.9 0.626	M10 ⅜	UC206D1 UC206-101D1 UC206-102D1 UC206-103D1 UC206-104D1
35 1¼ 1⅝ 1⅜ 1⅞	UCF207D1 UCF207-104D1 UCF207-105D1 UCF207-106D1 UCF207-107D1	117 4⅞	92 3⅝	19 ¾	15 19/32	34 1⅞	14 35/64	44.4 1¾	42.9 1.6890	17.5 0.689	M12 7/16	UC207D1 UC207-104D1 UC207-105D1 UC207-106D1 UC207-107D1
40 1½ 1⅞	UCF208D1 UCF208-108D1 UCF208-109D1	130 5⅝	102 4⅞	21 53/64	15 19/32	36 1⅝	16 5/8	51.2 2⅞	49.2 1.9370	19 0.748	M14 ½	UC208D1 UC208-108D1 UC208-109D1
45 1⅝ 1⅞ 1¾	UCF209D1 UCF209-110D1 UCF209-111D1 UCF209-112D1	137 5⅝	105 4⅞	22 55/64	16 5/8	38 1½	16 5/8	52.2 2⅞	49.2 1.9370	19 0.748	M14 ½	UC209D1 UC209-110D1 UC209-111D1 UC209-112D1

Remarks: 1) These numbers indicate relubricatable type. If maintenance free type is needed, please order without suffix "D1".

Note: Please refer to page 44 for size of grease fitting.