

G-LIST No. **EW1046**

**FXコート2刃 ショート**

FX Coated • 2 Flutes • Short

**FX-MG-TPDS**



(単位:mm) (Unit:mm)

ツール No. EDP No.	外径×刃部テーパ半角 Dc × θc	全長 L	刃長 ℓ	沖刃径 Ds	大端径 D1	在庫 Stock	重量 weight	標準価格 (Yen)
	<b>0.2 × 0.25°</b>	40	0.8	3	0.21	<input type="checkbox"/>	—	—
8536802	<b>0.2 × 0.5°</b>				0.21	D	6	15,700
	<b>0.2 × 0.75°</b>				0.22	<input type="checkbox"/>	—	—
8536812	<b>0.2 × 1°</b>				0.23	D	7	15,700
8536822	<b>0.2 × 1.5°</b>				0.24		6	15,700
8536832	<b>0.2 × 2°</b>				0.26		6	15,700
8536842	<b>0.2 × 2.5°</b>				0.27		6	15,700
8536852	<b>0.2 × 3°</b>				0.28		6	15,700
8536862	<b>0.2 × 4°</b>				0.31		6	16,600
8536882	<b>0.2 × 5°</b>				0.34		9	18,800
8536892	<b>0.2 × 7°</b>				0.4		9	20,300
8536912	<b>0.2 × 10°</b>				0.48		9	22,400
	<b>0.3 × 0.25°</b>	0.31	<input type="checkbox"/>	—	—			
8536803	<b>0.3 × 0.5°</b>	0.32	D	6	13,300			
	<b>0.3 × 0.75°</b>	0.33	<input type="checkbox"/>	—	—			
8536813	<b>0.3 × 1°</b>	0.34	D	9	13,300			
8536823	<b>0.3 × 1.5°</b>	0.36		6	13,300			
8536833	<b>0.3 × 2°</b>	0.38		6	13,300			
8536843	<b>0.3 × 2.5°</b>	0.4		6	13,300			
8536853	<b>0.3 × 3°</b>	0.43		6	13,300			
8536863	<b>0.3 × 4°</b>	0.47		6	14,300			
8536883	<b>0.3 × 5°</b>	0.51		9	15,100			
8536893	<b>0.3 × 7°</b>	0.59		9	17,100			
8536913	<b>0.3 × 10°</b>	0.72		9	18,800			
	<b>0.4 × 0.25°</b>	0.41		<input type="checkbox"/>	—	—		
8536804	<b>0.4 × 0.5°</b>	0.43		D	6	13,300		
	<b>0.4 × 0.75°</b>	0.44		<input type="checkbox"/>	—	—		
8536814	<b>0.4 × 1°</b>	0.46	D	6	13,300			
8536824	<b>0.4 × 1.5°</b>	0.48		6	13,300			
8536834	<b>0.4 × 2°</b>	0.51		6	13,300			
8536844	<b>0.4 × 2.5°</b>	0.54		6	13,300			
8536854	<b>0.4 × 3°</b>	0.57		6	13,300			
8536864	<b>0.4 × 4°</b>	0.62		6	14,300			
8536884	<b>0.4 × 5°</b>	0.68		9	15,100			
8536894	<b>0.4 × 7°</b>	0.79		9	17,100			
8536914	<b>0.4 × 10°</b>	0.96		9	18,800			
	<b>0.5 × 0.25°</b>	0.52		<input type="checkbox"/>	—	—		
8536805	<b>0.5 × 0.5°</b>	0.53		D	6	13,300		
	<b>0.5 × 0.75°</b>	0.55		<input type="checkbox"/>	—	—		
8536815	<b>0.5 × 1°</b>	0.57	D	9	13,300			
8536825	<b>0.5 × 1.5°</b>	0.6		6	13,300			
8536835	<b>0.5 × 2°</b>	0.64		6	13,300			
8536845	<b>0.5 × 2.5°</b>	0.67		6	13,300			
8536855	<b>0.5 × 3°</b>	0.71		6	13,300			
8536865	<b>0.5 × 4°</b>	0.78		6	14,300			
8536885	<b>0.5 × 5°</b>	0.85		9	15,100			
8536035	<b>0.5 × 6°</b>	0.92		7	16,100			
8536895	<b>0.5 × 7°</b>	0.99		9	17,100			
8536915	<b>0.5 × 10°</b>	1.21		9	18,800			
8536935	<b>0.5 × 12°</b>	1.35		9	19,300			
8536955	<b>0.5 × 15°</b>	1.57		7	20,300			
8536165	<b>0.5 × 20°</b>	1.96	10	22,200				
	<b>0.6 × 0.25°</b>	0.62	<input type="checkbox"/>	—	—			
8536806	<b>0.6 × 0.5°</b>	0.63	D	6	12,500			
	<b>0.6 × 0.75°</b>	0.65	<input type="checkbox"/>	—	—			
8536816	<b>0.6 × 1°</b>	0.67	D	9	12,500			

形状寸法表 超硬エンドミル

超硬テーパシリーズ CARBIDE TAPER SERIES

FXコーティングにより高効率、長寿命を実現しました。一般材から焼き入れ鋼まで幅広い対応が可能です。

FX coating improves productivity and tool life. Applicable for materials such as general and quenched steels.

●マークの説明はP1をご覧ください。  
See page 1 for explanation of icons.



(単位:mm) (Unit:mm)

ツール No. EDP No.	外径×刃部テーパ半角 Dc × θc	全長 L	刃長 ℓ	沖刃径 Ds	大端径 D1	在庫 Stock	重量 weight	標準価格 (Yen)
8536826	<b>0.6 × 1.5°</b>	40	3	3	0.7	<input type="checkbox"/>	6	12,500
8536836	<b>0.6 × 2°</b>				0.74	6	12,500	
8536846	<b>0.6 × 2.5°</b>				0.77	6	12,500	
8536856	<b>0.6 × 3°</b>				0.81	6	12,500	
8536866	<b>0.6 × 4°</b>				0.88	6	13,500	
8536886	<b>0.6 × 5°</b>				0.95	9	14,700	
8536036	<b>0.6 × 6°</b>				1.02	7	15,800	
8536896	<b>0.6 × 7°</b>				1.09	9	16,800	
8536916	<b>0.6 × 10°</b>				1.31	9	17,900	
8536936	<b>0.6 × 12°</b>				1.45	9	18,700	
8536956	<b>0.6 × 15°</b>				1.67	7	19,200	
8536166	<b>0.6 × 20°</b>				45	4	2.06	10
	<b>0.7 × 0.25°</b>	40	2	3	0.72	<input type="checkbox"/>	—	—
8536807	<b>0.7 × 0.5°</b>				0.73	D	6	12,500
	<b>0.7 × 0.75°</b>				0.75	<input type="checkbox"/>	—	—
8536817	<b>0.7 × 1°</b>				0.77	D	6	12,500
8536827	<b>0.7 × 1.5°</b>				0.8		6	12,500
8536837	<b>0.7 × 2°</b>				0.84		6	12,500
8536847	<b>0.7 × 2.5°</b>				0.87		6	12,500
8536857	<b>0.7 × 3°</b>				0.91		6	12,500
8536867	<b>0.7 × 4°</b>				0.98		6	13,500
8536887	<b>0.7 × 5°</b>				1.05		9	14,700
8536037	<b>0.7 × 6°</b>				1.12		7	15,800
8536897	<b>0.7 × 7°</b>				1.19		9	16,800
8536917	<b>0.7 × 10°</b>	1.41	9	17,900				
8536937	<b>0.7 × 12°</b>	1.55	9	18,700				
8536957	<b>0.7 × 15°</b>	1.77	7	19,200				
8536167	<b>0.7 × 20°</b>	45	4	2.16	14	20,300		
	<b>0.8 × 0.25°</b>	40	3	3	0.83	<input type="checkbox"/>	—	—
8536808	<b>0.8 × 0.5°</b>				0.83	D	6	12,500
	<b>0.8 × 0.75°</b>				0.88	<input type="checkbox"/>	—	—
8536818	<b>0.8 × 1°</b>				0.87	D	6	12,500
8536828	<b>0.8 × 1.5°</b>				0.9		6	12,500
8536838	<b>0.8 × 2°</b>				0.94		6	12,500
8536848	<b>0.8 × 2.5°</b>				1.06		6	12,500
8536858	<b>0.8 × 3°</b>				1.01		6	12,500
8536868	<b>0.8 × 4°</b>				1.08		6	13,500
8536888	<b>0.8 × 5°</b>				1.15		9	14,700
8536038	<b>0.8 × 6°</b>				1.22		7	15,800
8536898	<b>0.8 × 7°</b>				1.29		9	16,800
8536918	<b>0.8 × 10°</b>	1.51	9	17,900				
8536938	<b>0.8 × 12°</b>	1.65	9	18,700				
8536958	<b>0.8 × 15°</b>	1.87	7	19,200				
8536168	<b>0.8 × 20°</b>	50	4	2.26	14	20,300		
	<b>0.9 × 0.25°</b>	40	2	3	0.93	<input type="checkbox"/>	—	—
8536809	<b>0.9 × 0.5°</b>				0.93	D	6	12,500
	<b>0.9 × 0.75°</b>				0.98	<input type="checkbox"/>	—	—
8536819	<b>0.9 × 1°</b>				0.97	D	6	12,500
8536829	<b>0.9 × 1.5°</b>				1		6	12,500
8536839	<b>0.9 × 2°</b>				1.04		6	12,500
8536849	<b>0.9 × 2.5°</b>				1.16		6	12,500
8536859	<b>0.9 × 3°</b>				1.11		6	12,500
8536869	<b>0.9 × 4°</b>				1.18		6	13,500
8536889	<b>0.9 × 5°</b>				1.25		9	14,700
8536039	<b>0.9 × 6°</b>				1.32		7	15,800
8536899	<b>0.9 × 7°</b>				1.39		9	16,800

切削油剤はP896をご参照下さい。Cutting Fluid: Please refer to P896.

