


**G-LIST No FL1066**

**肩削りカッタ  
ねじ込みタイプ**

Shoulder Cutter Screw Fit Type

**PSE ねじ込みタイプ**



■形状寸法表 Specification Chart

(単位:mm) (Unit:mm)

ツール No. EDP No.	呼び Designation	外径 Dc	刃数 z	取付け径 Da	ねじサイズ Dg	スパナサイズ Spanner Size	全長 ℓ <sub>2</sub>	端面径 D	適用インサート Applicable Inserts	在庫 Stock	標準価格 (Yen)
7801600	PSE11R016SF8-2	16	2	8.5	8	10	27	14.5	ZD*11T3...	C	38,500
7801601	PSE11R020SF10-3	20	3	10.5	10	14	33	18		C	52,200
7801602	PSE11R025SF12-4	25	4	12.5	12	17	35	23		C	63,600
7801603	PSE11R028SF12-4	28	4	12.5	12	17	35	23		C	63,600
7801604	PSE11R032SF16-5	32	5	17	16	22	40	28		C	78,100
7801605	PSE11R035SF16-5	35	5	17	16	22	40	28		C	78,100
7801606	PSE11R040SF16-6	40	6	17	16	22	40	28	ZDKT1505...	C	84,600
7801607	PSE15R025SF12-2	25	2	12.5	12	17	35	23		C	46,300
7801608	PSE15R028SF12-2	28	2	12.5	12	17	35	23		C	46,300
7801609	PSE15R032SF16-3	32	3	17	16	22	40	28		C	63,600
7801610	PSE15R035SF16-3	35	3	17	16	22	40	28		C	63,600
7801611	PSE15R040SF16-4	40	4	17	16	22	40	28		C	72,800

※シャンクホルダはP640~642をご参照ください。


※Please see P640~642 for shank holders.

**G-LIST No FL1065**

**丸駒カッタ  
ねじ込みタイプ**

Radius Cutter Screw Fit Type

**PRC ねじ込みタイプ**



■形状寸法表 Specification Chart

(単位:mm) (Unit:mm)

ツール No. EDP No.	呼び Designation	外径 Dc	カッタ 外径 D1	刃数 z	取付け径 Da	ねじサイズ Dg	スパナサイズ Spanner Size	全長 ℓ <sub>2</sub>	端面径 D	適用インサート Applicable Inserts	在庫 Stock	標準価格 (Yen)
7801700	PRC10R020SF10-2	10	20	2	10.5	10	14	33	18	RPH*10T3...	C	47,300
7801701	PRC10R025SF12-3	15	25	3	12.5	12	17	35	23		C	58,800
7801702	PRC10R030SF16-3	20	30	3	17	16	22	40	28		C	65,200
7801703	PRC10R032SF16-4	22	32	4	17	16	22	40	28		C	72,500
7801704	PRC10R040SF16-4	30	40	4	17	16	22	40	28		C	80,200
7801705	PRC12R030SF16-2	18	30	2	17	16	22	40	28	RPH*1204...	C	69,500
7801706	PRC12R032SF16-3	20	32	3	17	16	22	40	28		C	72,200
7801707	PRC12R040SF16-3	28	40	3	17	16	22	40	28		C	72,200

※シャンクホルダはP640~642をご参照ください。

※Please see P640~642 for shank holders.