

BIMETAL THERMOMETERS MODEL BM-S-90S/BM-T-90S/BM-T-75S



BM-S-90S



BM-T-90S



BM-T-75S


SPECIFICATIONS

Cat. No.	2030-B	2010-B	2110-B
Model	BM-S-90S	BM-T-90S	BM-T-75S
Case dia.	103 mm		80 mm
Dial dia.	90 mm		75 mm
Materials Case	SUS304		
Window	Glass		
Sensing stem	Ø8 mm		
Materials	SUS304		
Screw	PT1/2		
Materials	SUS304		
Withstand pressure	5 kgf/cm ²		2 kgf/cm ²


* "B" in the catalog number is replaced with branch numbers shown below according to the measuring range and the stem length of your choice.

Measuring range	Stem length	BM-S-90S	BM-T-90S	BM-T-75S
-30 to 50°C (div. 1/1)	60mm	2030-20	2010-10	2110-10
	100mm	2030-22	2010-12	2110-12
	150mm	2030-24	2010-14	2110-14
	200mm	2030-26	2010-16	—
0 to 100°C (div. 2/1)	50mm	2030-40	2010-30	2110-20
	100mm	2030-42	2010-32	2110-22
	150mm	2030-44	2010-34	2110-24
	200mm	2030-46	2010-36	—
0 to 150°C (div. 2/1)	50mm	2030-60	2010-50	—
	100mm	2030-62	2010-52	—
	150mm	2030-64	2010-54	—
	200mm	2030-66	2010-56	—
0 to 200°C (div. 5/1)	50mm	—	2010-70	—
	100mm	—	2010-72	—
	150mm	—	2010-74	—
	200mm	—	2010-76	—

BM-S-90S



BM-T-90S



BM-T-75S

