


CoroDrill® 452 solid-carbide reamer

For handheld machines

CNSC 0



						M	N	S	O	Dimensions, mm, inch									
						H10E	H10E	H10E	H10E	DCON	DCON"	OAL	OAL"	LF	LF"	LCF	LCF"		BSG
DC	DC"	LU	LU"	CZC _{MS}	Ordering code	☆	☆	☆	☆										
4.17	.164	37.0	1.455	4	452.R-0417-032A0-C	☆	☆	☆	☆	4.17	.164	101	4.000	87.8	3.455	55	2.200	0.060	COROMANT
4.17	.164	38.1	1.500	4	452.R-0417-032A0-CM	☆	☆	☆	☆	4.17	.164	101	4.000	88.9	3.500	55	2.200	0.030	COROMANT
4.83	.190	37.0	1.455	4	452.R-0483-032A0-C	☆	☆	☆	☆	4.83	.190	101	4.000	87.8	3.455	55	2.200	0.060	COROMANT
4.83	.190	38.1	1.500	4	452.R-0483-032A0-CM	☆	☆	☆	☆	4.83	.190	101	4.000	88.9	3.500	55	2.200	0.030	COROMANT
5.56	.219	37.0	1.455	7/32	452.R-0556-032A0-C	☆	☆	☆	☆	5.56	.219	101	4.000	87.8	3.455	55	2.200	0.080	COROMANT
5.56	.219	38.1	1.500	7/32	452.R-0556-032A0-CM	☆	☆	☆	☆	5.56	.219	101	4.000	88.9	3.500	55	2.200	0.035	COROMANT
6.35	.250	37.0	1.455	1/4	452.R-0635-032A0-C	☆	☆	☆	☆	6.35	.250	101	4.000	87.8	3.455	55	2.200	0.080	COROMANT
6.35	.250	38.1	1.500	1/4	452.R-0635-032A0-CM	☆	☆	☆	☆	6.35	.250	101	4.000	88.9	3.500	55	2.200	0.035	COROMANT
7.94	.313	33.8	1.331	5/16	452.R-0794-029A0-C	☆	☆	☆	☆	7.94	.313	101	4.000	84.6	3.331	55	2.200	0.130	COROMANT
7.94	.313	35.0	1.376	5/16	452.R-0794-029A0-CM	☆	☆	☆	☆	7.94	.313	101	4.000	85.8	3.376	55	2.200	0.400	COROMANT
9.53	.375	30.6	1.205	3/8	452.R-0953-025A0-C	☆	☆	☆	☆	9.53	.375	101	4.000	81.4	3.205	55	2.200	0.130	COROMANT
9.53	.375	31.8	1.250	3/8	452.R-0953-025A0-CM	☆	☆	☆	☆	9.53	.375	101	4.000	82.6	3.250	55	2.200	0.400	COROMANT
11.12	.438	30.6	1.205	7/16	452.R-1112-025A0-C	☆	☆	☆	☆	11.12	.438	101	4.000	81.4	3.205	55	2.200	0.180	COROMANT
11.12	.438	31.8	1.250	7/16	452.R-1112-025A0-CM	☆	☆	☆	☆	11.12	.438	101	4.000	82.6	3.250	55	2.200	0.050	COROMANT
12.71	.500	30.6	1.205	1/2	452.R-1270-025A0-C	☆	☆	☆	☆	12.70	.500	101	4.000	81.4	3.205	55	2.200	0.180	COROMANT
12.71	.500	31.8	1.250	1/2	452.R-1270-025A0-CM	☆	☆	☆	☆	12.70	.500	101	4.000	82.6	3.250	55	2.200	0.050	COROMANT

