


肩削りカッタ

Shoulder Cutter

PSE インサート **NEW SIZES**

■適用インサート Applicable Inserts

(単位:mm) (Unit:mm)

	呼び Designation	切れ刃数 No. of Cutting Edges	インサート寸法 Insert Size						超硬 Uncoated	コーティング材種 Grade of Coated Materials						標準価格 (Yen)
			A×B	厚さ T	逃げ角 α°	R	おしり刃 (副切れ刃) b	CK010		XP3035	XP2040	XC1015	XC5035	XC5040	XP6015	
①	ZDKT11T302FR-NM	2	10×6.8	3.8	15	0.2	2.0	7811048								1,670
	ZDKT11T304FR-NM	2	10×6.8	3.8	15	0.4	1.8	7811049								1,670
	ZDHT11T304FR-NM	2	10×6.8	3.5	15	0.4	1.8	7811024								3,630
	ZDKT11T308SR-GL	2	10×6.8	3.8	15	0.8	1.4		7814026	7813026						1,320
	ZDKT11T304SR-GM	2	10×6.8	3.8	15	0.4	1.8		7814025	7813025	7812025					1,320
	ZDKT11T308SR-GM	2	10×6.8	3.8	15	0.8	1.4		7814032	7813032						1,320
	ZDKT11T312SR-GM	2	10×6.8	3.8	15	1.2	1.0		7814053							1,320
	ZDKT11T320SR-GM	2	10×6.8	3.8	15	2.0	2.1		7814038							1,320
	ZDKT11T330SR-GM	2	10×6.8	3.8	15	3.0	1.5		7814054							1,320
	ZDKT11T340SR-GM	2	10×6.8	3.8	15	4.0	—		7814055							1,320
	ZDKT11T308SR-GR	2	10×6.8	3.8	15	0.8	1.4		7814033	7813033	7812033					1,320
	NEW ZDKT11T308SR-HR	2	10×6.8	3.8	15	0.8	1.4								7824035	1,670
②	ZDKT11T304ER-SM	2	10×6.8	3.8	15	0.4	1.8							7816034		2,630
	ZDKT11T308ER-SM	2	10×6.8	3.8	15	0.8	1.4					7815031	7816031			2,630
	ZDKT11T316ER-SM	2	10×6.8	3.8	15	1.6	0.8					7815027	7816027			2,630
	ZDKT150508FR-NM	2	14×9.3	5.56	15	0.8	1.6	7811046								1,970
	ZDKT150508SR-GL	2	14×9.3	5.56	15	0.8	1.6		7814057	7813057						1,790
	ZDKT150508SR-GM	2	14×9.3	5.56	15	0.8	1.6		7814029	7813028	7812029					1,790
	NEW ZDKT150512SR-GM	2	14×9.3	5.56	15	1.2	1.2		7814077							1,790
	NEW ZDKT150516SR-GM	2	14×9.3	5.56	15	1.6	0.8		7814078							1,790
	NEW ZDKT150520SR-GM	2	14×9.3	5.56	15	2.0	2.1		7814079							1,790
	NEW ZDKT150530SR-GM	2	14×9.3	5.56	15	3.0	1.9		7814080							1,790
	NEW ZDKT150540SR-GM	2	14×9.3	5.56	15	4.0	1.1		7814081							1,790
	NEW ZDKT150550SR-GM	2	14×9.3	5.56	15	5.0	0.7		7814082							1,790
	ZDKT150508SR-GR	2	14×9.3	5.56	15	0.8	1.6		7814058	7813058	7812058					1,790
	NEW ZDKT150508SR-HR	2	14×9.3	5.56	15	0.8	1.6								7824036	1,790
	ZDKT150508ER-SM	2	14×9.3	5.56	15	0.8	1.6					7815056	7816056			3,450

在庫区分はすべてC (標準在庫品) となります。 Stocks are categorized as C (standard stock item).

・コーナR=R2 以上のインサートを使用する場合、カッタボディのコーナ部を修正する必要があります。

ボディ側のコーナ R = インサートの R - 1 (例: インサート R3 の場合ボディには R2 の R)

When using an insert with a corner radius of R2 or greater, the corner of the cutter body must be adjusted.

The body corner radius should be equal to insert radius minus 1 (example: if insert radius is R3, body radius should be R2).

■部品 Accessories

	ツール No. EDP No.	在庫 Stock	呼び Designation	適用インサート Applicable Inserts	適用カッタ Applicable Cutters
クランプねじ Clamping Screw	7808107	C	FS25656P (Torx 8IP)	① ZD*T11...	PSE SS/SF φ16-35
	7808109	C	FS25673P (Torx 8IP)	① ZD*T11...	PSE BORE φ40-80
	7808115	C	FS35686P (Torx 15IP)	② ZDKT15...	PSE SS/SF φ25-63 PSE BORE φ40-125
パワースクリュー Power Screw	7808150	C	PS0830 (M8X30)	① ZD*T11... ② ZDKT15...	PSE BORE φ40
	7808151	C	PS1031 (M10X31)	① ZD*T11...	PSE BORE φ50
				② ZDKT15...	

	ツール No. EDP No.	在庫 Stock	呼び Designation	適用インサート Applicable Inserts	適用カッタ Applicable Cutters	標準価格 (Yen)
レンチ Wrench	7808225	C	8IP-D (Torx 8IP)	① ZD*T11...	PSE SS/SF φ16-35 PSE BORE φ40-80	1,290
	7808228	C	15IP-D (Torx 15IP)	② ZDKT15...	PSE SS/SF φ25-63 PSE BORE φ40-125	1,510

レンチは別途ご購入下さい。 The wrenches are sold separately from the cutters.