


**G-LIST No. FL1072**

**ねじ込みタイプ専用  
ストレートシャンクホルダ**

Holder for Screw Fit Type


**OP-SFA**



鋼シャンク Steel shank

(単位:mm) (Unit:mm)

ツール No. EDP No.	呼び Designation	シャンク径 D <sub>s</sub>	首径 D <sub>2</sub>	ねじサイズ M	取付け径 D <sub>a</sub>	全長 L	首下長 L <sub>f</sub>	在庫 Stock	標準価格 (Yen)
7801904	SF-M06SS10-4	10	9	6	6.5	104	4	C	16,800
7801905	SF-M06SS12-10	12	11	6	6.5	104	10	C	19,500
7801900	SF-M08SS16-15	16	14.5	8	8.5	95	15	C	21,900
7801901	SF-M10SS20-20	20	18	10	10.5	120	20	C	23,100
7801902	SF-M12SS25-35	25	23	12	12.5	135	35	C	24,600
7801903	SF-M16SS32-35	32	28	16	17	155	35	C	26,800



オール超硬シャンク All carbide shank

(単位:mm) (Unit:mm)

ツール No. EDP No.	呼び Designation	シャンク径 D <sub>s</sub>	首径 D <sub>2</sub>	ねじサイズ M	取付け径 D <sub>a</sub>	全長 L	首下長 L <sub>f</sub>	在庫 Stock	標準価格 (Yen)
7801918	SF-M06SS10-24CS	10	9	6	6.5	124	24	C	27,300
7801919	SF-M06SS12-34CS	12	11	6	6.5	134	34	C	31,600
7801910	SF-M08SS16-55CS	16	14.5	8	8.5	115	55	C	36,300
7801911	SF-M08SS16-85CS	16	14.5	8	8.5	145	85	C	43,300
7801912	SF-M10SS20-70CS	20	18	10	10.5	140	70	C	51,800
7801913	SF-M10SS20-110CS	20	18	10	10.5	180	110	C	62,300
7801914	SF-M12SS25-90CS	25	23	12	12.5	170	90	C	77,100
7801915	SF-M12SS25-140CS	25	23	12	12.5	220	140	C	95,700
7801916	SF-M16SS32-120CS	32	28	16	17	220	120	C	122,000
7801917	SF-M16SS32-190CS	32	28	16	17	290	190	C	160,000