



CoroCut® 1-2 blade for parting

Spring-lock design


N123..A2




N123..A2 (C)



N123..A2 (S)



Double ended parting blade

								Dimensions, mm, inch					
	SSC	CZC _{MS}	CDX	CUTDIA	OHX	CNSC	Ordering code	H	LF	WF	HF		MIID
	D	21	15.0	30.0	30.0	0	N123D15-21A2	25.9	110.0	1.3	21.4	0.0	N123D2-0150-0002-CM
			.591	1.181	1.181			1.020	4.331	.049	.843		
	25		15.0		55.0	0	N123D15-25A2	31.9	150.0	1.3	25.0	0.1	N123D2-0150-0002-CM
			.591		2.165			1.256	5.906	.049	.984		
	E	21	15.0	30.0	30.0	0	N123E15-21A2	25.9	110.0	1.8	21.4	0.1	N123E2-0200-0002-CM
			.591	1.181	1.181			1.020	4.331	.069	.843		
	25		20.0		55.0	0	N123E20-25A2	31.9	150.0	1.8	25.0	0.1	N123E2-0200-0002-CM
			.787		2.165			1.256	5.906	.069	.984		
F	21		30.0		30.0	0	N123F30-21A2	25.9	110.0	2.3	21.4	0.0	N123F2-0250-0002-CM
			1.181		1.181			1.020	4.331	.089	.843		
	25		55.0		55.0	0	N123F55-25A2	31.9	150.0	2.3	25.0	0.1	N123F2-0250-0002-CM
		2.165		2.165			1.256	5.906	.089	.984			
G	21		30.0		30.0	0	N123G30-21A2	25.9	110.0	2.7	21.4	0.1	N123G2-0300-0003-TF
			1.181		1.181			1.020	4.331	.105	.843		
	25		55.0		55.0	0	N123G55-25A2	31.9	150.0	2.3	25.0	0.1	N123G2-0300-0003-TF
		2.165		2.165			1.256	5.906	.089	.984			
H	25		55.0		55.0	0	N123H55-25A2	31.9	150.0	3.7	25.0	0.1	N123H2-0400-0004-TF
			2.165		2.165			1.256	5.906	.145	.984		
J	25		55.0		55.0	0	N123J55-25A2	31.9	150.0	4.8	25.0	0.1	N123J2-0500-0002-CM
			2.165		2.165			1.256	5.906	.187	.984		
K	25		55.0		55.0	0	N123K55-25A2	31.9	150.0	5.8	25.0	0.1	N123K2-0600-0004-CR
			2.165		2.165			1.256	5.906	.226	.984		

SSC = To correspond with SSC on insert.

