


PKVD Twin Triple Run Tee

RoHS compliant



Unit : mm

Model code	Tube O.D. $\phi D1$	Tube O.D. $\phi D2$	R	A	B	E	L1	L2	J	$\phi P1$	$\phi P2$	$\phi P3$	Tube end C1	Tube end C2	Hex. H	Orifice bore (ϕ mm)	Weight (g)	CAD file name
PKVD8-4-02④	8	4	R1/4	11	69.2	19.2	32	31.2	10	14.5	14.5	10	18.1	14.9	14	3	32	PKVD8-4-02_
PKVD8-4-03④			R3/8	12	72.2		34.7				18				17		46	PKVD8-4-03_
PKVD8-6-02④		6	R1/4	11	76.9	21.3	36.5	34.4	12.5		14.5	12.5		17	14	4.6	41	PKVD8-6-02_
PKVD8-6-03④			R3/8	12	80.7		39.9				18				17		52	PKVD8-6-03_
PKVD10-6-03④	10	6	R3/8	12	81.5	22.3	38.2	37	12.5	17.5	18	12.5	20.2	17	17	4.6	56	PKVD10-6-03_
PKVD10-6-04④			R1/2	15	85.5		40.3				20				21		78	PKVD10-6-04_
PKVD10-8-03④		8	R3/8	12	87.8	23.7	41.5	40	14.5		18			18.1	17	6.7	65	PKVD10-8-03_
PKVD10-8-04④			R1/2	15	91.8		43.6				20	14.5			21		87	PKVD10-8-04_

※ 1. ④ in Model code / Replaced with "W" for Light-gray color, "-C" for Clean-room package, "W-C" for Light-gray color and Clean-room package, "-UC" for Clean-wash and Clean-room package

※ 2. "L1" is a reference value for height dimension after tightening thread.

※ 3. Orifice bore is the smallest passage converted in terms of the diameter.

FITTING
CONTROLLER
VALVE
TUBE

MAKE-TO-ORDER
PRODUCTS

68

Standard
Series

Mini
Series

Stainless
Series

Chemical
Series

PP
Series

EG
Series

Anti-siphon
& Brass Series

Die Temperature
Control

Minimal
Series

Step Fitting
Series

Rotary
Series

Twist-Proof
Fitting

Block and
Connector

Coupling

Color
Cap